

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224788

Luminaire Tested: **LSSQWM2B20FL409030D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20FL409030D010 2LBDL*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1402.7 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224788

CATALOG NUMBER: LSSQWM2B20FL409030D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224788

CATALOG NUMBER: LSSQWM2B20FL409030D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	99		108	104	101	98		101	98	96		98	96	94		95	94	92
3	105	100	96	93		104	99	95	92		96	93	90		94	91	89		92	90	88
4	101	95	90	87		100	94	90	86		92	88	85		90	87	85		88	86	84
5	98	91	86	82		96	90	85	82		88	84	81		86	83	80		85	82	80
6	94	86	82	78		93	86	81	78		84	80	77		83	79	77		82	79	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	76	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1269875
5°	1246730
10°	1108301
15°	871635
20°	580014
25°	332979
30°	168218
35°	79110
40°	31856
45°	15776
50°	8677
55°	6078
60°	5578
65°	3300
70°	4077
75°	2694
80°	4015
85°	0



TEST NUMBER: P224788

CATALOG NUMBER: LSSQWM2B20FL409030D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.7	20.9
10°-20°	588.8	42.0
20°-30°	366.3	26.1
30°-40°	112.6	8.0
40°-50°	24.8	1.8
50°-60°	8.8	0.6
60°-70°	4.4	0.3
70°-80°	2.6	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1248.7	89.0
0°-40°	1361.4	97.1
0°-60°	1394.9	99.4
0°-90°	1402.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1402.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3278	
5°	3206	294
15°	2174	589
25°	779	366
35°	167	113
45°	29	25
55°	9	9
65°	4	4
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224788

CATALOG NUMBER: LSSQWM2B20FL409030D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3278.4
2.5°	3264.0
5°	3206.4
7.5°	3060.7
10°	2817.8
12.5°	2526.3
15°	2173.6
17.5°	1788.6
20°	1407.1
22.5°	1067.0
25°	779.1
27.5°	548.8
30°	376.1
32.5°	253.7
35°	167.3
37.5°	100.8
40°	63.0
42.5°	43.2
45°	28.8
47.5°	19.8
50°	14.4
52.5°	12.6
55°	9.0
57.5°	7.2
60°	7.2
62.5°	5.4
65°	3.6
67.5°	3.6
70°	3.6
72.5°	3.6
75°	1.8
77.5°	1.8
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)