

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225328

Luminaire Tested: **LSSQ2B15FL409040D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225328
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B15FL409040D010 2LBDC*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1028.9 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225328

CATALOG NUMBER: LSSQ2B15FL409040D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P225328

CATALOG NUMBER: LSSQ2B15FL409040D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86	86	86	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79	79	79	79
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	931567
5°	914596
10°	813035
15°	639411
20°	425478
25°	244253
30°	123401
35°	58067
40°	23361
45°	11558
50°	6388
55°	4457
60°	4106
65°	2383
70°	2945
75°	1946
80°	2900
85°	0



TEST NUMBER: P225328

CATALOG NUMBER: LSSQ2B15FL409040D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.4	20.9
10°-20°	431.9	42.0
20°-30°	268.7	26.1
30°-40°	82.6	8.0
40°-50°	18.2	1.8
50°-60°	6.5	0.6
60°-70°	3.2	0.3
70°-80°	1.9	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	916.1	89.0
0°-40°	998.7	97.1
0°-60°	1023.3	99.5
0°-90°	1028.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1028.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2405	
5°	2352	215
15°	1594	432
25°	572	269
35°	123	83
45°	21	18
55°	7	6
65°	3	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P225328

CATALOG NUMBER: LSSQ2B15FL409040D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2405.0
2.5°	2394.4
5°	2352.2
7.5°	2245.3
10°	2067.1
12.5°	1853.2
15°	1594.5
17.5°	1312.1
20°	1032.2
22.5°	782.7
25°	571.5
27.5°	402.6
30°	275.9
32.5°	186.1
35°	122.8
37.5°	73.9
40°	46.2
42.5°	31.7
45°	21.1
47.5°	14.5
50°	10.6
52.5°	9.2
55°	6.6
57.5°	5.3
60°	5.3
62.5°	4.0
65°	2.6
67.5°	2.6
70°	2.6
72.5°	2.6
75°	1.3
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)