

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224994

Luminaire Tested: **LSR2WM2B20FL409730D010 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224994
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL409730D010 2LBDL*LI
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1298.5 lumens
Efficiency: N/A
Efficacy: 62.1 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224994

CATALOG NUMBER: LSR2WM2B20FL409730D010 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P224994

CATALOG NUMBER: LSR2WM2B20FL409730D010 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	105	103		102	101	100		99	98	97
2	110	106	103	100		108	104	101	99		101	99	97		98	96	95		96	94	93
3	106	101	96	93		104	99	95	92		97	94	91		94	92	90		92	90	88
4	102	96	91	88		100	95	90	87		93	89	86		91	88	85		89	86	84
5	98	91	86	83		97	90	86	83		89	85	82		87	84	81		86	83	81
6	94	87	82	79		93	86	82	79		85	81	78		84	80	78		83	79	77
7	91	83	79	75		90	83	78	75		82	78	75		81	77	74		80	76	74
8	88	80	75	72		87	80	75	72		79	74	71		78	74	71		77	73	71
9	85	77	72	69		84	76	72	69		76	71	69		75	71	68		74	71	68
10	82	74	69	66		81	74	69	66		73	69	66		72	68	66		72	68	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1245588
5°	1197000
10°	1041987
15°	813649
20°	541101
25°	309857
30°	154039
35°	70787
40°	28417
45°	12983
50°	6026
55°	3377
60°	1937
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224994

CATALOG NUMBER: LSR2WM2B20FL409730D010 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	280.2	21.6
10°-20°	550.2	42.4
20°-30°	340.5	26.2
30°-40°	101.9	7.8
40°-50°	20.4	1.6
50°-60°	5.0	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1170.9	90.2
0°-40°	1272.8	98.0
0°-60°	1298.2	100.0
0°-90°	1298.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1298.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3216	
5°	3078	280
15°	2029	550
25°	725	340
35°	150	102
45°	24	20
55°	5	5
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224994

CATALOG NUMBER: LSR2WM2B20FL409730D010 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3215.7
1°	3198.3
2°	3182.0
3°	3149.6
4°	3119.6
5°	3078.5
6°	3022.3
7°	2951.2
8°	2860.1
9°	2756.5
10°	2649.2
11°	2538.1
12°	2419.6
13°	2296.1
14°	2163.8
15°	2029.0
17.5°	1673.4
20°	1312.7
22.5°	993.3
25°	725.0
27.5°	509.1
30°	344.4
32.5°	227.1
35°	149.7
37.5°	93.6
40°	56.2
42.5°	36.2
45°	23.7
47.5°	15.0
50°	10.0
52.5°	7.5
55°	5.0
57.5°	3.7
60°	2.5
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224994

CATALOG NUMBER: LSR2WM2B20FL409730D010 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)