

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222577

Luminaire Tested: **LSSQWM2B15NFL259040D010 2LBDL\*H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P222577  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B15NFL259040D010 2LBDL\*H  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
NARROW FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1100.8 lumens  
Efficiency: N/A  
Efficacy: 77.0 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P222577

CATALOG NUMBER: LSSQWM2B15NFL259040D010 2LBDL\*H

### Luminous Intensity Polar Plot





TEST NUMBER: P222577

CATALOG NUMBER: LSSQWM2B15NFL259040D010 2LBDL\*H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |    |    |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0  |    |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10 | 0  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 99 | 97 |
| 1   | 115 | 113 | 112 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 | 104 | 103 | 102 | 100 | 100 | 99  | 97  | 97  | 96 | 95 |
| 2   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 104 | 102 | 100 | 101 | 99  | 98  | 98  | 97  | 96  | 95  | 95  | 94 | 92 |
| 3   | 109 | 105 | 101 | 99  | 107 | 103 | 100 | 98  | 101 | 98  | 96  | 99  | 97  | 95  | 96  | 95  | 93  | 92  | 92  | 91 | 90 |
| 4   | 106 | 101 | 97  | 95  | 104 | 100 | 97  | 94  | 98  | 95  | 93  | 96  | 94  | 92  | 95  | 93  | 91  | 90  | 89  | 88 | 86 |
| 5   | 103 | 98  | 94  | 91  | 102 | 97  | 94  | 91  | 95  | 92  | 90  | 94  | 91  | 89  | 93  | 90  | 89  | 88  | 87  | 86 | 84 |
| 6   | 101 | 95  | 91  | 89  | 99  | 94  | 91  | 88  | 93  | 90  | 88  | 92  | 89  | 87  | 91  | 88  | 87  | 86  | 85  | 84 | 82 |
| 7   | 98  | 92  | 89  | 86  | 97  | 92  | 88  | 86  | 91  | 88  | 85  | 90  | 87  | 85  | 89  | 86  | 85  | 84  | 83  | 82 | 80 |
| 8   | 96  | 90  | 86  | 84  | 95  | 90  | 86  | 84  | 89  | 86  | 83  | 88  | 85  | 83  | 87  | 85  | 83  | 82  | 81  | 80 | 79 |
| 9   | 94  | 88  | 84  | 82  | 93  | 88  | 84  | 82  | 87  | 84  | 82  | 86  | 83  | 81  | 85  | 83  | 81  | 80  | 79  | 79 | 79 |
| 10  | 92  | 86  | 82  | 80  | 91  | 86  | 82  | 80  | 85  | 82  | 80  | 84  | 82  | 80  | 84  | 81  | 79  | 79  | 79  | 79 | 79 |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2529602 |
| 5°  | 2335636 |
| 10° | 1580916 |
| 15° | 537875  |
| 20° | 197570  |
| 25° | 104710  |
| 30° | 53851   |
| 35° | 25109   |
| 40° | 8242    |
| 45° | 4163    |
| 50° | 1989    |
| 55° | 743     |
| 60° | 852     |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P222577

CATALOG NUMBER: LSSQWM2B15NFL259040D010 2LBDL\*H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 511.0  | 46.4      |
| 10°-20°   | 429.6  | 39.0      |
| 20°-30°   | 117.9  | 10.7      |
| 30°-40°   | 34.4   | 3.1       |
| 40°-50°   | 6.4    | 0.6       |
| 50°-60°   | 1.5    | 0.1       |
| 60°-70°   | 0.1    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1058.5 | 96.2      |
| 0°-40°    | 1092.9 | 99.3      |
| 0°-60°    | 1100.7 | 100.0     |
| 0°-90°    | 1100.8 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1100.8 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 6531 |      |
| 5°  | 6007 | 511  |
| 15° | 1341 | 430  |
| 25° | 245  | 118  |
| 35° | 53   | 34   |
| 45° | 8    | 6    |
| 55° | 1    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P222577

CATALOG NUMBER: LSSQWM2B15NFL259040D010 2LBDL\*H

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 6530.6 |
| 1°    | 6492.7 |
| 2°    | 6425.5 |
| 3°    | 6329.0 |
| 4°    | 6196.7 |
| 5°    | 6006.9 |
| 6°    | 5747.8 |
| 7°    | 5423.6 |
| 8°    | 5027.8 |
| 9°    | 4560.5 |
| 10°   | 4019.4 |
| 11°   | 3426.3 |
| 12°   | 2809.4 |
| 13°   | 2220.6 |
| 14°   | 1718.6 |
| 15°   | 1341.3 |
| 17.5° | 756.8  |
| 20°   | 479.3  |
| 22.5° | 341.5  |
| 25°   | 245.0  |
| 27.5° | 173.5  |
| 30°   | 120.4  |
| 32.5° | 84.6   |
| 35°   | 53.1   |
| 37.5° | 21.7   |
| 40°   | 16.3   |
| 42.5° | 11.9   |
| 45°   | 7.6    |
| 47.5° | 4.3    |
| 50°   | 3.3    |
| 52.5° | 2.2    |
| 55°   | 1.1    |
| 57.5° | 1.1    |
| 60°   | 1.1    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P222577

CATALOG NUMBER: LSSQWM2B15NFL259040D010 2LBDL\*H

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |  |     |
|-------|--|-----|
| 85°   |  | 0.0 |
| 87.5° |  | 0.0 |



(END OF REPORT)