

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224477

Luminaire Tested: **LSSQWM2B20FL409730D010 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224477
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20FL409730D010 2LBDL*WH
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1321.3 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224477

CATALOG NUMBER: LSSQWM2B20FL409730D010 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P224477

CATALOG NUMBER: LSSQWM2B20FL409730D010 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	100		108	104	101	98		101	98	96			98	96	94			95
3	106	100	96	93		104	99	95	92		96	93	91			94	91	89			92
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			88
5	98	91	86	82		96	90	85	82		88	84	81			87	83	81			85
6	94	87	82	78		93	86	81	78		85	80	77			83	80	77			82
7	91	83	78	75		89	82	78	74		81	77	74			80	76	74			79
8	87	79	75	71		86	79	74	71		78	74	71			77	73	70			76
9	84	76	71	68		83	76	71	68		75	71	68			74	70	68			73
10	81	73	69	65		80	73	68	65		72	68	65			71	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1219094
5°	1172970
10°	1032429
15°	810963
20°	551365
25°	321952
30°	163969
35°	77597
40°	33878
45°	14681
50°	7050
55°	4525
60°	2556
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224477

CATALOG NUMBER: LSSQWM2B20FL409730D010 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.5	20.9
10°-20°	549.9	41.6
20°-30°	353.0	26.7
30°-40°	112.0	8.5
40°-50°	23.9	1.8
50°-60°	6.1	0.5
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1178.4	89.2
0°-40°	1290.4	97.7
0°-60°	1320.5	99.9
0°-90°	1321.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1321.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3147	
5°	3017	276
15°	2022	550
25°	753	353
35°	164	112
45°	27	24
55°	7	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224477

CATALOG NUMBER: LSSQWM2B20FL409730D010 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3147.3
2.5°	3117.1
5°	3016.7
7.5°	2852.6
10°	2624.9
12.5°	2347.1
15°	2022.3
17.5°	1675.7
20°	1337.6
22.5°	1021.2
25°	753.3
27.5°	537.4
30°	366.6
32.5°	246.1
35°	164.1
37.5°	108.8
40°	67.0
42.5°	41.9
45°	26.8
47.5°	18.4
50°	11.7
52.5°	8.4
55°	6.7
57.5°	5.0
60°	3.3
62.5°	1.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)