

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225105

Luminaire Tested: **LSR2B15FL408050D010 2LBD\*WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225105  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14829)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2B15FL408050D010 2LBD\*WH  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
SPUN ROUND TRIM WITH WHEAT HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1465.4 lumens  
Efficiency: N/A  
Efficacy: 102.5 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225105

CATALOG NUMBER: LSR2B15FL408050D010 2LBD\*WH

### Luminous Intensity Polar Plot





TEST NUMBER: P225105

CATALOG NUMBER: LSR2B15FL408050D010 2LBD\*WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87		
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82		
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79		
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75		
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72		
8	87	79	75	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69		
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66		
10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1352070
5°	1300933
10°	1145077
15°	899425
20°	611506
25°	357084
30°	181859
35°	86061
40°	37569
45°	16269
50°	7834
55°	4997
60°	2866
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225105

CATALOG NUMBER: LSR2B15FL408050D010 2LBD\*WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	305.6	20.9
10°-20°	609.9	41.6
20°-30°	391.5	26.7
30°-40°	124.2	8.5
40°-50°	26.5	1.8
50°-60°	6.8	0.5
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1307.0	89.2
0°-40°	1431.2	97.7
0°-60°	1464.5	99.9
0°-90°	1465.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1465.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3491	
5°	3346	306
15°	2243	610
25°	836	391
35°	182	124
45°	30	27
55°	7	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225105

CATALOG NUMBER: LSR2B15FL408050D010 2LBD\*WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3490.6
2.5°	3457.2
5°	3345.8
7.5°	3163.8
10°	2911.3
12.5°	2603.1
15°	2242.9
17.5°	1858.6
20°	1483.5
22.5°	1132.6
25°	835.5
27.5°	596.0
30°	406.6
32.5°	272.9
35°	182.0
37.5°	120.7
40°	74.3
42.5°	46.4
45°	29.7
47.5°	20.4
50°	13.0
52.5°	9.3
55°	7.4
57.5°	5.6
60°	3.7
62.5°	1.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)