

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B15WFL558050D010 2LBD*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29153)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15WFL558050D010 2LBD*LI
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1370.2 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.8
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSR2B15WFL558050D010 2LBD*LI

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL558050D010 2LBD*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93																																				
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																																				
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																																				
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75																																				
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																																				
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																																				
7	83	73	67	63	82	73	67	63	72	66	63	70	66	62	69	65	62	61																																				
8	79	69	63	59	78	69	63	59	68	62	59	66	62	58	66	61	58	57																																				
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53																																				
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	705551
5°	676323
10°	610828
15°	535148
20°	456599
25°	383026
30°	298731
35°	205979
40°	132277
45°	80032
50°	46943
55°	26337
60°	7515
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL558050D010 2LBD*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.0	11.7
10°-20°	370.9	27.1
20°-30°	407.6	29.7
30°-40°	275.8	20.1
40°-50°	118.2	8.6
50°-60°	36.1	2.6
60°-70°	1.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	938.5	68.5
0°-40°	1214.3	88.6
0°-60°	1368.7	99.9
0°-90°	1370.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1370.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1822	
5°	1739	160
15°	1334	371
25°	896	408
35°	436	276
45°	146	118
55°	39	36
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL558050D010 2LBD*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1821.5
1°	1811.8
2°	1796.5
3°	1781.2
4°	1761.7
5°	1739.4
6°	1711.6
7°	1678.2
8°	1637.9
9°	1596.1
10°	1553.0
11°	1507.1
12°	1465.3
13°	1422.2
14°	1379.0
15°	1334.5
17.5°	1219.0
20°	1107.7
22.5°	1001.9
25°	896.2
27.5°	787.6
30°	667.9
32.5°	546.9
35°	435.6
37.5°	340.9
40°	261.6
42.5°	197.6
45°	146.1
47.5°	107.1
50°	77.9
52.5°	55.7
55°	39.0
57.5°	25.0
60°	9.7
62.5°	1.4
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL558050D010 2LBD*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)