

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225055

Luminaire Tested: **LSR2B20FL408035D010 2LBD*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225055
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14830)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B20FL408035D010 2LBD*WMH
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1763.7 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225055

CATALOG NUMBER: LSR2B20FL408035D010 2LBD*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P225055

CATALOG NUMBER: LSR2B20FL408035D010 2LBD*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87		
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	83		
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79		
6	94	87	82	78	93	86	81	78	85	81	77	83	80	77	82	79	77	75		
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72		
8	87	79	75	71	86	79	74	71	78	74	71	77	73	71	76	73	70	69		
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66		
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1600436
5°	1567434
10°	1388543
15°	1091148
20°	733601
25°	426192
30°	212989
35°	100436
40°	47480
45°	20816
50°	10787
55°	6010
60°	3486
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225055

CATALOG NUMBER: LSR2B20FL408035D010 2LBD*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	368.8	20.9
10°-20°	738.0	41.8
20°-30°	466.5	26.5
30°-40°	145.9	8.3
40°-50°	33.9	1.9
50°-60°	8.9	0.5
60°-70°	1.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1573.4	89.2
0°-40°	1719.3	97.5
0°-60°	1762.1	99.9
0°-90°	1763.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1763.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4132	
5°	4031	369
15°	2721	738
25°	997	467
35°	212	146
45°	38	34
55°	9	9
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225055

CATALOG NUMBER: LSR2B20FL408035D010 2LBD*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4131.8
2.5°	4111.7
5°	4031.2
7.5°	3841.1
10°	3530.3
12.5°	3161.4
15°	2721.0
17.5°	2240.3
20°	1779.7
22.5°	1354.9
25°	997.2
27.5°	704.3
30°	476.2
32.5°	317.5
35°	212.4
37.5°	143.1
40°	93.9
42.5°	58.1
45°	38.0
47.5°	26.8
50°	17.9
52.5°	13.4
55°	8.9
57.5°	6.7
60°	4.5
62.5°	4.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)