

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSRWM2B15WFL558050D010 2LBD\*H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29157)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSRWM2B15WFL558050D010 2LBD\*H  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
WIDE FLOOD OPTIC  
SPUN ROUND TRIM WITH HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1363.0 lumens  
Efficiency: N/A  
Efficacy: 95.3 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#  
CATALOG NUMBER: LSRWM2B15WFL558050D010 2LBD\*H

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B15WFL558050D010 2LBD\*H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 | 101 | 99  | 98  | 97  | 96  | 95  | 93  |
| 2   | 108 | 103 | 99  | 95  | 105 | 101 | 97  | 94  | 98  | 95  | 92  | 95  | 92  | 90  | 92  | 90  | 88  | 87  |
| 3   | 102 | 96  | 91  | 86  | 100 | 94  | 90  | 86  | 92  | 88  | 84  | 89  | 86  | 83  | 87  | 84  | 82  | 80  |
| 4   | 97  | 89  | 83  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  | 84  | 80  | 77  | 82  | 79  | 76  | 74  |
| 5   | 92  | 83  | 77  | 73  | 90  | 82  | 77  | 73  | 81  | 76  | 72  | 79  | 75  | 71  | 77  | 74  | 71  | 69  |
| 6   | 87  | 78  | 72  | 68  | 86  | 77  | 71  | 67  | 76  | 71  | 67  | 74  | 70  | 66  | 73  | 69  | 66  | 64  |
| 7   | 83  | 73  | 67  | 63  | 81  | 73  | 67  | 63  | 71  | 66  | 62  | 70  | 65  | 62  | 69  | 65  | 62  | 60  |
| 8   | 79  | 69  | 63  | 59  | 77  | 68  | 63  | 59  | 67  | 62  | 58  | 66  | 62  | 58  | 65  | 61  | 58  | 56  |
| 9   | 75  | 65  | 59  | 55  | 74  | 65  | 59  | 55  | 64  | 58  | 55  | 63  | 58  | 55  | 62  | 58  | 54  | 53  |
| 10  | 71  | 62  | 56  | 52  | 70  | 61  | 55  | 52  | 60  | 55  | 52  | 59  | 55  | 51  | 59  | 54  | 51  | 50  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 660928 |
| 5°  | 652644 |
| 10° | 600995 |
| 15° | 528972 |
| 20° | 453013 |
| 25° | 382214 |
| 30° | 298418 |
| 35° | 206168 |
| 40° | 132428 |
| 45° | 80909  |
| 50° | 47847  |
| 55° | 27283  |
| 60° | 8599   |
| 65° | 1283   |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B15WFL558050D010 2LBD\*H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 155.5  | 11.4      |
| 10°-20°   | 366.5  | 26.9      |
| 20°-30°   | 406.4  | 29.8      |
| 30°-40°   | 275.8  | 20.2      |
| 40°-50°   | 119.0  | 8.7       |
| 50°-60°   | 37.4   | 2.7       |
| 60°-70°   | 2.4    | 0.2       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 928.4  | 68.1      |
| 0°-40°    | 1204.2 | 88.3      |
| 0°-60°    | 1360.6 | 99.8      |
| 0°-90°    | 1363.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1363.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1706 |      |
| 5°  | 1678 | 156  |
| 15° | 1319 | 367  |
| 25° | 894  | 406  |
| 35° | 436  | 276  |
| 45° | 148  | 119  |
| 55° | 40   | 37   |
| 65° | 1    | 2    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B15WFL558050D010 2LBD\*H

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1706.3 |
| 1°    | 1702.2 |
| 2°    | 1696.6 |
| 3°    | 1693.8 |
| 4°    | 1688.2 |
| 5°    | 1678.5 |
| 6°    | 1663.2 |
| 7°    | 1639.5 |
| 8°    | 1607.4 |
| 9°    | 1569.8 |
| 10°   | 1528.0 |
| 11°   | 1486.3 |
| 12°   | 1444.5 |
| 13°   | 1402.7 |
| 14°   | 1360.9 |
| 15°   | 1319.1 |
| 17.5° | 1206.3 |
| 20°   | 1099.0 |
| 22.5° | 997.3  |
| 25°   | 894.3  |
| 27.5° | 787.0  |
| 30°   | 667.2  |
| 32.5° | 546.0  |
| 35°   | 436.0  |
| 37.5° | 341.3  |
| 40°   | 261.9  |
| 42.5° | 197.8  |
| 45°   | 147.7  |
| 47.5° | 108.6  |
| 50°   | 79.4   |
| 52.5° | 57.1   |
| 55°   | 40.4   |
| 57.5° | 26.5   |
| 60°   | 11.1   |
| 62.5° | 2.8    |
| 65°   | 1.4    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B15WFL558050D010 2LBD\*H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |  |     |
|-------|--|-----|
| 85°   |  | 0.0 |
| 87.5° |  | 0.0 |



(END OF REPORT)