

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224950

Luminaire Tested: **LSSQ2B15FL408050D010 2LBD\*H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224950  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQ2B15FL408050D010 2LBD\*H  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
SPUN ROUND TRIM WITH HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1438.5 lumens  
Efficiency: N/A  
Efficacy: 100.6 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224950

CATALOG NUMBER: LSSQ2B15FL408050D010 2LBD\*H

### Luminous Intensity Polar Plot





TEST NUMBER: P224950

CATALOG NUMBER: LSSQ2B15FL408050D010 2LBD\*H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	103	100	108	104	101	99	101	99	97	98	96	94	96	94	93	91			
3	106	100	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87			
4	102	96	91	88	100	94	90	87	92	89	86	91	88	85	89	86	84	83			
5	98	91	86	83	96	90	86	82	89	85	82	87	84	81	86	83	80	79			
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76			
7	91	83	78	75	90	83	78	75	82	77	74	80	77	74	79	76	74	73			
8	88	80	75	72	87	79	75	72	78	74	71	77	74	71	77	73	71	70			
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67			
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1334252
5°	1306337
10°	1150504
15°	902634
20°	599428
25°	344091
30°	172556
35°	79677
40°	32412
45°	14516
50°	7533
55°	4727
60°	2169
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224950

CATALOG NUMBER: LSSQ2B15FL408050D010 2LBD\*H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	306.8	21.3
10°-20°	609.2	42.4
20°-30°	378.6	26.3
30°-40°	114.2	7.9
40°-50°	23.3	1.6
50°-60°	6.0	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1294.6	90.0
0°-40°	1408.8	97.9
0°-60°	1438.2	100.0
0°-90°	1438.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1438.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3445	
5°	3360	307
15°	2251	609
25°	805	379
35°	168	114
45°	26	23
55°	7	6
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224950

CATALOG NUMBER: LSSQ2B15FL408050D010 2LBD\*H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3444.6
1°	3433.5
2°	3418.2
3°	3407.0
4°	3390.3
5°	3359.7
6°	3310.9
7°	3244.1
8°	3147.9
9°	3039.3
10°	2925.1
11°	2803.9
12°	2677.1
13°	2544.8
14°	2400.0
15°	2250.9
17.5°	1851.2
20°	1454.2
22.5°	1103.2
25°	805.1
27.5°	568.3
30°	385.8
32.5°	253.5
35°	168.5
37.5°	104.5
40°	64.1
42.5°	41.8
45°	26.5
47.5°	16.7
50°	12.5
52.5°	8.4
55°	7.0
57.5°	4.2
60°	2.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224950

CATALOG NUMBER: LSSQ2B15FL408050D010 2LBD\*H

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)