

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQ2B15WFL558050D010 2LBD\**MW***

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQ2B15WFL558050D010 2LBD\*MW  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
WIDE FLOOD OPTIC  
SPUN ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1372.1 lumens  
Efficiency: N/A  
Efficacy: 95.9 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#  
CATALOG NUMBER: LSSQ2B15WFL558050D010 2LBD\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15WFL558050D010 2LBD\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																											
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86																											
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80																											
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74																											
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69																											
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64																											
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60																											
8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56																											
9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	53																											
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	643575
5°	639501
10°	594505
15°	521915
20°	449881
25°	384736
30°	305306
35°	212835
40°	134653
45°	82168
50°	48570
55°	26607
60°	5810
65°	5133
70°	4304
75°	5687
80°	4238
85°	8444



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15WFL558050D010 2LBD\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.6	11.1
10°-20°	362.5	26.4
20°-30°	408.9	29.8
30°-40°	282.9	20.6
40°-50°	120.6	8.8
50°-60°	34.9	2.5
60°-70°	5.1	0.4
70°-80°	3.3	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	924.0	67.3
0°-40°	1206.9	88.0
0°-60°	1362.4	99.3
0°-90°	1372.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1372.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1662	
5°	1645	153
15°	1302	362
25°	900	409
35°	450	283
45°	150	121
55°	39	35
65°	6	5
75°	4	3
85°	2	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15WFL558050D010 2LBD\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1661.5
2.5°	1659.7
5°	1644.7
7.5°	1594.0
10°	1511.5
12.5°	1410.2
15°	1301.5
17.5°	1189.0
20°	1091.4
22.5°	999.5
25°	900.2
27.5°	795.1
30°	682.6
32.5°	560.7
35°	450.1
37.5°	348.8
40°	266.3
42.5°	200.7
45°	150.0
47.5°	108.8
50°	80.6
52.5°	58.1
55°	39.4
57.5°	16.9
60°	7.5
62.5°	5.6
65°	5.6
67.5°	3.8
70°	3.8
72.5°	3.8
75°	3.8
77.5°	1.9
80°	1.9
82.5°	1.9
85°	1.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)