

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223171

Luminaire Tested: **LSR2WM2B20NFL258040D010 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223171
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20NFL258040D010 2LBDC*MB
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1916.3 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223171

CATALOG NUMBER: LSR2WM2B20NFL258040D010 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P223171

CATALOG NUMBER: LSR2WM2B20NFL258040D010 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	115	113	112	110		113	111	110	108		107	106	105			104	103	102			97
2	112	109	106	104		110	107	104	102		104	102	100			101	99	98			95
3	109	105	101	99		107	103	100	98		101	98	96			99	97	95			92
4	106	101	97	95		104	100	97	94		98	95	93			96	94	92			90
5	103	98	94	91		102	97	94	91		95	92	90			94	91	89			88
6	101	95	91	89		99	94	91	88		93	90	88			92	89	87			86
7	98	92	89	86		97	92	88	86		91	88	85			90	87	85			84
8	96	90	86	84		95	90	86	84		89	86	83			88	85	83			82
9	94	88	84	82		93	88	84	82		87	84	82			86	83	81			80
10	92	86	82	80		91	86	82	80		85	82	80			84	82	80			79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4403620
5°	4065949
10°	2752109
15°	936318
20°	343903
25°	182324
30°	93703
35°	43740
40°	14310
45°	7231
50°	3435
55°	1283
60°	1472
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223171

CATALOG NUMBER: LSR2WM2B20NFL258040D010 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	889.5	46.4
10°-20°	747.9	39.0
20°-30°	205.3	10.7
30°-40°	59.8	3.1
40°-50°	11.1	0.6
50°-60°	2.5	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1842.6	96.2
0°-40°	1902.5	99.3
0°-60°	1916.1	100.0
0°-90°	1916.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1916.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11369	
5°	10457	890
15°	2335	748
25°	427	205
35°	92	60
45°	13	11
55°	2	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223171

CATALOG NUMBER: LSR2WM2B20NFL258040D010 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	11368.7
1°	11302.6
2°	11185.6
3°	11017.6
4°	10787.3
5°	10457.0
6°	10005.9
7°	9441.5
8°	8752.5
9°	7939.0
10°	6997.1
11°	5964.6
12°	4890.6
13°	3865.7
14°	2991.8
15°	2334.9
17.5°	1317.5
20°	834.3
22.5°	594.6
25°	426.6
27.5°	302.0
30°	209.5
32.5°	147.2
35°	92.5
37.5°	37.8
40°	28.3
42.5°	20.8
45°	13.2
47.5°	7.6
50°	5.7
52.5°	3.8
55°	1.9
57.5°	1.9
60°	1.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223171

CATALOG NUMBER: LSR2WM2B20NFL258040D010 2LBDC*MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)