

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224955

Luminaire Tested: **LSSQWM2B20FL408040D010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224955
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20FL408040D010 2LBD*H
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1952.6 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224955

CATALOG NUMBER: LSSQWM2B20FL408040D010 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224955

CATALOG NUMBER: LSSQWM2B20FL408040D010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	103	100		108	104	101	99		101	99	97			98	96	94			91
3	106	100	96	93		104	99	95	92		97	94	91			94	92	90			87
4	102	96	91	88		100	94	90	87		92	89	86			91	88	85			83
5	98	91	86	83		96	90	86	82		89	85	82			87	84	81			79
6	94	87	82	79		93	86	82	78		85	81	78			84	80	77			76
7	91	83	78	75		90	83	78	75		82	77	74			80	77	74			73
8	88	80	75	72		87	79	75	72		78	74	71			77	74	71			70
9	85	77	72	69		84	76	72	69		75	71	68			75	71	68			67
10	82	74	69	66		81	73	69	66		73	69	66			72	68	66			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1811114
5°	1773200
10°	1561683
15°	1225246
20°	813651
25°	467051
30°	234235
35°	108191
40°	43991
45°	19666
50°	10244
55°	6416
60°	2944
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224955

CATALOG NUMBER: LSSQWM2B20FL408040D010 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	416.5	21.3
10°-20°	827.0	42.4
20°-30°	513.8	26.3
30°-40°	155.0	7.9
40°-50°	31.7	1.6
50°-60°	8.2	0.4
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1757.3	90.0
0°-40°	1912.3	97.9
0°-60°	1952.1	100.0
0°-90°	1952.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1952.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4676	
5°	4560	417
15°	3055	827
25°	1093	514
35°	229	155
45°	36	32
55°	10	8
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224955

CATALOG NUMBER: LSSQWM2B20FL408040D010 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4675.7
1°	4660.6
2°	4639.8
3°	4624.6
4°	4602.0
5°	4560.4
6°	4494.2
7°	4403.4
8°	4273.0
9°	4125.5
10°	3970.5
11°	3806.0
12°	3633.9
13°	3454.3
14°	3257.7
15°	3055.4
17.5°	2512.7
20°	1973.9
22.5°	1497.4
25°	1092.8
27.5°	771.4
30°	523.7
32.5°	344.1
35°	228.8
37.5°	141.8
40°	87.0
42.5°	56.7
45°	35.9
47.5°	22.7
50°	17.0
52.5°	11.3
55°	9.5
57.5°	5.7
60°	3.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224955

CATALOG NUMBER: LSSQWM2B20FL408040D010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)