

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225403

Luminaire Tested: **LSR2B15FL409050D010 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225403
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15FL409050D010 2LBDC*MB
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1201.4 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225403

CATALOG NUMBER: LSR2B15FL409050D010 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225403

CATALOG NUMBER: LSR2B15FL409050D010 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																			
2	110	106	103	100	108	104	101	99	101	99	96	98	96	94	96	94	92	91																			
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87																			
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83																			
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79																			
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76																			
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72																			
8	87	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	69																			
9	84	77	72	69	83	76	72	68	75	71	68	74	71	68	74	70	68	67																			
10	82	74	69	66	81	73	69	66	73	68	65	72	68	65	71	68	65	64																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1087009
5°	1068104
10°	952860
15°	753177
20°	502189
25°	291351
30°	145810
35°	68612
40°	26799
45°	11942
50°	5664
55°	3174
60°	1240
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225403

CATALOG NUMBER: LSR2B15FL409050D010 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	251.8	21.0
10°-20°	508.4	42.3
20°-30°	319.8	26.6
30°-40°	97.8	8.1
40°-50°	19.2	1.6
50°-60°	4.3	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1080.0	89.9
0°-40°	1177.7	98.0
0°-60°	1201.2	100.0
0°-90°	1201.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1201.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2806	
5°	2747	252
15°	1878	508
25°	682	320
35°	145	98
45°	22	19
55°	5	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225403

CATALOG NUMBER: LSR2B15FL409050D010 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2806.3
2.5°	2800.1
5°	2747.0
7.5°	2622.3
10°	2422.6
12.5°	2173.0
15°	1878.2
17.5°	1550.6
20°	1218.3
22.5°	934.4
25°	681.7
27.5°	480.5
30°	326.0
32.5°	220.0
35°	145.1
37.5°	88.9
40°	53.0
42.5°	34.3
45°	21.8
47.5°	14.0
50°	9.4
52.5°	6.2
55°	4.7
57.5°	3.1
60°	1.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)