

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSRWM2B15FL409050D010 2LBD*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B15FL409050D010 2LBD*LI
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1217.6 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSRWM2B15FL409050D010 2LBD*LI

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B15FL409050D010 2LBD*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96																											
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91																											
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87																											
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83																											
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79																											
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76																											
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73																											
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70																											
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67																											
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1168003
5°	1122423
10°	977050
15°	762962
20°	507424
25°	290539
30°	144468
35°	66390
40°	26647
45°	12161
50°	5664
55°	3174
60°	1782
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B15FL409050D010 2LBD*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	262.7	21.6
10°-20°	515.9	42.4
20°-30°	319.3	26.2
30°-40°	95.6	7.8
40°-50°	19.1	1.6
50°-60°	4.7	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1097.9	90.2
0°-40°	1193.5	98.0
0°-60°	1217.3	100.0
0°-90°	1217.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1217.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3015	
5°	2887	263
15°	1903	516
25°	680	319
35°	140	96
45°	22	19
55°	5	5
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B15FL409050D010 2LBD*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3015.4
1°	2999.0
2°	2983.8
3°	2953.4
4°	2925.3
5°	2886.7
6°	2834.0
7°	2767.3
8°	2681.9
9°	2584.8
10°	2484.1
11°	2380.0
12°	2268.8
13°	2153.0
14°	2029.0
15°	1902.6
17.5°	1569.1
20°	1231.0
22.5°	931.4
25°	679.8
27.5°	477.4
30°	323.0
32.5°	213.0
35°	140.4
37.5°	87.8
40°	52.7
42.5°	33.9
45°	22.2
47.5°	14.0
50°	9.4
52.5°	7.0
55°	4.7
57.5°	3.5
60°	2.3
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B15FL409050D010 2LBD*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)