

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B20WFL558040D010 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14807)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20WFL558040D010 2LBDL*H
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1710.4 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL558040D010 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL558040D010 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	111	108	106		111	108	106	104		104	102	101			101	99	98			97
2	108	102	98	95		105	101	97	94		98	94	92			95	92	90			92
3	102	95	90	86		100	94	89	85		91	87	84			89	85	83			86
4	96	89	83	79		95	87	82	78		85	81	77			83	79	76			81
5	91	83	77	72		90	82	76	72		80	75	71			78	74	71			77
6	87	77	71	67		85	77	71	67		75	70	66			74	69	66			72
7	82	73	66	62		81	72	66	62		71	65	62			69	65	61			68
8	78	68	62	58		77	68	62	58		67	61	57			66	61	57			65
9	74	64	58	54		73	64	58	54		63	58	54			62	57	54			61
10	71	61	55	51		70	60	55	51		60	54	51			59	54	51			58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	802387
5°	786827
10°	731421
15°	647551
20°	560599
25°	471239
30°	369041
35°	263668
40°	176065
45°	109175
50°	65382
55°	39168
60°	17586
65°	2291
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL558040D010 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.8	11.0
10°-20°	449.7	26.3
20°-30°	501.6	29.3
30°-40°	351.4	20.5
40°-50°	160.4	9.4
50°-60°	53.6	3.1
60°-70°	5.8	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1139.2	66.6
0°-40°	1490.5	87.1
0°-60°	1704.6	99.7
0°-90°	1710.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1710.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2072	
5°	2024	188
15°	1615	450
25°	1103	502
35°	558	351
45°	199	160
55°	58	54
65°	2	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL558040D010 2LBDL*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2071.5
2.5°	2061.4
5°	2023.6
7.5°	1952.9
10°	1859.6
12.5°	1741.0
15°	1614.8
17.5°	1483.6
20°	1360.0
22.5°	1236.3
25°	1102.6
27.5°	966.4
30°	825.1
32.5°	686.3
35°	557.6
37.5°	444.1
40°	348.2
42.5°	264.9
45°	199.3
47.5°	148.9
50°	108.5
52.5°	78.2
55°	58.0
57.5°	40.4
60°	22.7
62.5°	7.6
65°	2.5
67.5°	2.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)