

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B20WFL558040D010 2LBDL\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B20WFL558040D010 2LBDL\*MW  
Description: 2000 Lumen, 2inch Portfolio LED Cylinder  
WIDE FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1722.6 lumens  
Efficiency: N/A  
Efficacy: 82.4 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL558040D010 2LBDL\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL558040D010 2LBDL\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 50  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 113 | 110 | 108 | 106 |  | 111 | 108 | 106 | 104 |  | 104 | 102 | 101 |  |  | 101 | 99  | 98  |  |  | 97  |
| 2   | 108 | 102 | 98  | 95  |  | 105 | 101 | 97  | 94  |  | 98  | 94  | 92  |  |  | 95  | 92  | 90  |  |  | 92  |
| 3   | 102 | 95  | 90  | 86  |  | 100 | 94  | 89  | 85  |  | 91  | 87  | 84  |  |  | 89  | 85  | 83  |  |  | 87  |
| 4   | 97  | 89  | 83  | 79  |  | 95  | 88  | 82  | 78  |  | 85  | 81  | 77  |  |  | 83  | 80  | 76  |  |  | 82  |
| 5   | 91  | 83  | 77  | 72  |  | 90  | 82  | 76  | 72  |  | 80  | 75  | 71  |  |  | 78  | 74  | 71  |  |  | 77  |
| 6   | 87  | 78  | 71  | 67  |  | 85  | 77  | 71  | 67  |  | 75  | 70  | 66  |  |  | 74  | 69  | 66  |  |  | 73  |
| 7   | 82  | 73  | 67  | 62  |  | 81  | 72  | 66  | 62  |  | 71  | 66  | 62  |  |  | 70  | 65  | 62  |  |  | 69  |
| 8   | 78  | 69  | 62  | 58  |  | 77  | 68  | 62  | 58  |  | 67  | 62  | 58  |  |  | 66  | 61  | 58  |  |  | 65  |
| 9   | 74  | 65  | 59  | 55  |  | 73  | 64  | 58  | 54  |  | 63  | 58  | 54  |  |  | 62  | 57  | 54  |  |  | 61  |
| 10  | 71  | 61  | 55  | 51  |  | 70  | 61  | 55  | 51  |  | 60  | 55  | 51  |  |  | 59  | 54  | 51  |  |  | 58  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 808004 |
| 5°  | 802847 |
| 10° | 746406 |
| 15° | 655250 |
| 20° | 564844 |
| 25° | 482992 |
| 30° | 383309 |
| 35° | 267214 |
| 40° | 169037 |
| 45° | 103204 |
| 50° | 60983  |
| 55° | 33361  |
| 60° | 7282   |
| 65° | 6507   |
| 70° | 5323   |
| 75° | 7034   |
| 80° | 5354   |
| 85° | 10666  |



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL558040D010 2LBDL\*MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 191.6  | 11.1      |
| 10°-20°   | 455.1  | 26.4      |
| 20°-30°   | 513.4  | 29.8      |
| 30°-40°   | 355.2  | 20.6      |
| 40°-50°   | 151.4  | 8.8       |
| 50°-60°   | 43.8   | 2.5       |
| 60°-70°   | 6.4    | 0.4       |
| 70°-80°   | 4.0    | 0.2       |
| 80°-90°   | 1.6    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1160.1 | 67.3      |
| 0°-40°    | 1515.3 | 88.0      |
| 0°-60°    | 1710.5 | 99.3      |
| 0°-90°    | 1722.6 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1722.6 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2086 |      |
| 5°  | 2065 | 192  |
| 15° | 1634 | 455  |
| 25° | 1130 | 513  |
| 35° | 565  | 355  |
| 45° | 188  | 151  |
| 55° | 49   | 44   |
| 65° | 7    | 6    |
| 75° | 5    | 4    |
| 85° | 2    | 2    |
| 90° | 0    |      |



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL558040D010 2LBDL\*MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2086.0 |
| 2.5°  | 2083.7 |
| 5°    | 2064.8 |
| 7.5°  | 2001.2 |
| 10°   | 1897.7 |
| 12.5° | 1770.5 |
| 15°   | 1634.0 |
| 17.5° | 1492.7 |
| 20°   | 1370.3 |
| 22.5° | 1254.9 |
| 25°   | 1130.1 |
| 27.5° | 998.3  |
| 30°   | 857.0  |
| 32.5° | 704.0  |
| 35°   | 565.1  |
| 37.5° | 437.9  |
| 40°   | 334.3  |
| 42.5° | 251.9  |
| 45°   | 188.4  |
| 47.5° | 136.6  |
| 50°   | 101.2  |
| 52.5° | 73.0   |
| 55°   | 49.4   |
| 57.5° | 21.2   |
| 60°   | 9.4    |
| 62.5° | 7.1    |
| 65°   | 7.1    |
| 67.5° | 4.7    |
| 70°   | 4.7    |
| 72.5° | 4.7    |
| 75°   | 4.7    |
| 77.5° | 2.4    |
| 80°   | 2.4    |
| 82.5° | 2.4    |
| 85°   | 2.4    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)