

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224779

Luminaire Tested: **LSSQWM2B15FL409050D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224779
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL409050D010 2LBDL*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1133.3 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224779

CATALOG NUMBER: LSSQWM2B15FL409050D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224779

CATALOG NUMBER: LSSQWM2B15FL409050D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91				91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86				86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82				82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79				79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75				75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72				72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69				69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66				66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64				64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1025886
5°	1007214
10°	895357
15°	704174
20°	468553
25°	268999
30°	135880
35°	63931
40°	25737
45°	12764
50°	6990
55°	4930
60°	4493
65°	2658
70°	3284
75°	2245
80°	3346
85°	0



TEST NUMBER: P224779

CATALOG NUMBER: LSSQWM2B15FL409050D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	237.2	20.9
10°-20°	475.7	42.0
20°-30°	295.9	26.1
30°-40°	91.0	8.0
40°-50°	20.0	1.8
50°-60°	7.1	0.6
60°-70°	3.6	0.3
70°-80°	2.1	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1008.8	89.0
0°-40°	1099.8	97.0
0°-60°	1126.9	99.4
0°-90°	1133.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1133.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2648	
5°	2590	237
15°	1756	476
25°	629	296
35°	135	91
45°	23	20
55°	7	7
65°	3	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P224779

CATALOG NUMBER: LSSQWM2B15FL409050D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2648.5
2.5°	2636.9
5°	2590.4
7.5°	2472.6
10°	2276.4
12.5°	2040.9
15°	1756.0
17.5°	1444.9
20°	1136.7
22.5°	862.0
25°	629.4
27.5°	443.4
30°	303.8
32.5°	205.0
35°	135.2
37.5°	81.4
40°	50.9
42.5°	34.9
45°	23.3
47.5°	16.0
50°	11.6
52.5°	10.2
55°	7.3
57.5°	5.8
60°	5.8
62.5°	4.4
65°	2.9
67.5°	2.9
70°	2.9
72.5°	2.9
75°	1.5
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)