

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222495

Luminaire Tested: **LSSQWM2B15NFL259050D010 2LBD*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15NFL259050D010 2LBD*WMH
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1199.6 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222495

CATALOG NUMBER: LSSQWM2B15NFL259050D010 2LBD*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P222495

CATALOG NUMBER: LSSQWM2B15NFL259050D010 2LBD*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	95
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	94	92
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	91	90
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	89	88	86
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	87	86	84
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	85	84	82
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84	83	82	80
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	81	80	79
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	79	78	77
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	78	77	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2756664
5°	2545291
10°	1722827
15°	586116
20°	215295
25°	114113
30°	58682
35°	27379
40°	8950
45°	4547
50°	2109
55°	810
60°	930
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222495

CATALOG NUMBER: LSSQWM2B15NFL259050D010 2LBD*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	556.8	46.4
10°-20°	468.2	39.0
20°-30°	128.5	10.7
30°-40°	37.5	3.1
40°-50°	6.9	0.6
50°-60°	1.6	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1153.5	96.2
0°-40°	1191.0	99.3
0°-60°	1199.5	100.0
0°-90°	1199.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1199.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7117	
5°	6546	557
15°	1462	468
25°	267	128
35°	58	37
45°	8	7
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222495

CATALOG NUMBER: LSSQWM2B15NFL259050D010 2LBD*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	7116.8
1°	7075.4
2°	7002.2
3°	6897.0
4°	6752.8
5°	6546.1
6°	6263.7
7°	5910.4
8°	5479.1
9°	4969.8
10°	4380.2
11°	3733.9
12°	3061.5
13°	2419.9
14°	1872.8
15°	1461.6
17.5°	824.8
20°	522.3
22.5°	372.2
25°	267.0
27.5°	189.1
30°	131.2
32.5°	92.2
35°	57.9
37.5°	23.6
40°	17.7
42.5°	13.0
45°	8.3
47.5°	4.7
50°	3.5
52.5°	2.4
55°	1.2
57.5°	1.2
60°	1.2
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222495

CATALOG NUMBER: LSSQWM2B15NFL259050D010 2LBD*WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)