

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B20WFL559040D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B20WFL559040D010 2LBDL*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1397.8 lumens
Efficiency: N/A
Efficacy: 66.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSR2B20WFL559040D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B20WFL559040D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																											
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86																											
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80																											
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74																											
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69																											
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64																											
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60																											
8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56																											
9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	53																											
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	655738
5°	651555
10°	605715
15°	531739
20°	458372
25°	391958
30°	311075
35°	216855
40°	137181
45°	83757
50°	49534
55°	27080
60°	5888
65°	5224
70°	4304
75°	5687
80°	4238
85°	8444



TEST NUMBER: P#

CATALOG NUMBER: LSR2B20WFL559040D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	11.1
10°-20°	369.3	26.4
20°-30°	416.6	29.8
30°-40°	288.2	20.6
40°-50°	122.9	8.8
50°-60°	35.5	2.5
60°-70°	5.2	0.4
70°-80°	3.3	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	941.5	67.4
0°-40°	1229.7	88.0
0°-60°	1388.1	99.3
0°-90°	1397.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1397.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1693	
5°	1676	156
15°	1326	369
25°	917	417
35°	459	288
45°	153	123
55°	40	36
65°	6	5
75°	4	3
85°	2	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B20WFL559040D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1692.9
2.5°	1691.0
5°	1675.7
7.5°	1624.1
10°	1540.0
12.5°	1436.9
15°	1326.0
17.5°	1211.4
20°	1112.0
22.5°	1018.4
25°	917.1
27.5°	810.1
30°	695.5
32.5°	571.3
35°	458.6
37.5°	355.4
40°	271.3
42.5°	204.4
45°	152.9
47.5°	110.8
50°	82.2
52.5°	59.2
55°	40.1
57.5°	17.2
60°	7.6
62.5°	5.7
65°	5.7
67.5°	3.8
70°	3.8
72.5°	3.8
75°	3.8
77.5°	1.9
80°	1.9
82.5°	1.9
85°	1.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)