

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQ2B20WFL559040D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B20WFL559040D010 2LBDC*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1499.5 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B20WFL559040D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B20WFL559040D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97
2	108	102	98	95	105	101	97	94	98	94	92		95	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		87
4	97	89	83	79	95	88	82	78	85	81	77		83	80	76		82
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	71	67	85	77	71	67	75	70	66		74	69	66		73
7	82	73	67	62	81	72	66	62	71	66	62		70	65	62		69
8	78	69	62	58	77	68	62	58	67	62	58		66	61	58		65
9	74	65	59	55	73	64	58	54	63	58	54		62	57	54		61
10	71	61	55	51	70	61	55	51	60	55	51		59	54	51		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	703459
5°	698953
10°	649806
15°	570437
20°	491719
25°	420508
30°	333707
35°	232601
40°	147193
45°	89838
50°	53089
55°	29039
60°	6352
65°	5591
70°	4643
75°	6136
80°	4461
85°	8889



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B20WFL559040D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.8	11.1
10°-20°	396.2	26.4
20°-30°	447.0	29.8
30°-40°	309.2	20.6
40°-50°	131.8	8.8
50°-60°	38.1	2.5
60°-70°	5.5	0.4
70°-80°	3.5	0.2
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1010.0	67.4
0°-40°	1319.2	88.0
0°-60°	1489.1	99.3
0°-90°	1499.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1499.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1816	
5°	1798	167
15°	1422	396
25°	984	447
35°	492	309
45°	164	132
55°	43	38
65°	6	6
75°	4	3
85°	2	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B20WFL559040D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1816.1
2.5°	1814.0
5°	1797.6
7.5°	1742.3
10°	1652.1
12.5°	1541.4
15°	1422.5
17.5°	1299.5
20°	1192.9
22.5°	1092.5
25°	983.9
27.5°	869.1
30°	746.1
32.5°	612.9
35°	491.9
37.5°	381.3
40°	291.1
42.5°	219.3
45°	164.0
47.5°	118.9
50°	88.1
52.5°	63.5
55°	43.0
57.5°	18.4
60°	8.2
62.5°	6.1
65°	6.1
67.5°	4.1
70°	4.1
72.5°	4.1
75°	4.1
77.5°	2.0
80°	2.0
82.5°	2.0
85°	2.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)