

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225023

Luminaire Tested: **LSSQWM2B20FL409040D010 2LBD\*WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225023  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14830)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B20FL409040D010 2LBD\*WMH  
Description: 2000 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1492.3 lumens  
Efficiency: N/A  
Efficacy: 71.4 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225023

CATALOG NUMBER: LSSQWM2B20FL409040D010 2LBD\*WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P225023

CATALOG NUMBER: LSSQWM2B20FL409040D010 2LBD\*WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87	87	87	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	79	79	79
6	94	87	82	78	93	86	81	78	85	81	77	83	80	77	82	79	77	75	75	75	75
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72	72	72	72
8	87	79	75	71	86	79	74	71	78	74	71	77	73	71	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1354162
5°	1326206
10°	1174890
15°	923245
20°	620698
25°	360588
30°	180205
35°	84973
40°	40199
45°	17639
50°	9099
55°	5132
60°	2944
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225023

CATALOG NUMBER: LSSQWM2B20FL409040D010 2LBD\*WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	312.1	20.9
10°-20°	624.4	41.8
20°-30°	394.7	26.5
30°-40°	123.5	8.3
40°-50°	28.7	1.9
50°-60°	7.6	0.5
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1331.2	89.2
0°-40°	1454.7	97.5
0°-60°	1490.9	99.9
0°-90°	1492.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1492.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3496	
5°	3411	312
15°	2302	624
25°	844	395
35°	180	123
45°	32	29
55°	8	8
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225023

CATALOG NUMBER: LSSQWM2B20FL409040D010 2LBD\*WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3496.0
2.5°	3479.0
5°	3410.8
7.5°	3250.0
10°	2987.1
12.5°	2675.0
15°	2302.3
17.5°	1895.5
20°	1505.8
22.5°	1146.4
25°	843.7
27.5°	595.9
30°	402.9
32.5°	268.6
35°	179.7
37.5°	121.1
40°	79.5
42.5°	49.2
45°	32.2
47.5°	22.7
50°	15.1
52.5°	11.4
55°	7.6
57.5°	5.7
60°	3.8
62.5°	3.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)