

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225057

Luminaire Tested: **LSR2WM2B20FL408050D010 2LBD*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225057
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14830)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL408050D010 2LBD*WMH
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1824.2 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225057

CATALOG NUMBER: LSR2WM2B20FL408050D010 2LBD*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P225057

CATALOG NUMBER: LSR2WM2B20FL408050D010 2LBD*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	100		108	104	101	98		101	98	96			98	96	94			91
3	106	100	96	93		104	99	95	92		96	93	91			94	91	89			87
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			83
5	98	91	86	82		96	90	85	82		88	84	81			87	83	81			79
6	94	87	82	78		93	86	81	78		85	81	77			83	80	77			75
7	91	83	78	75		89	82	78	74		81	77	74			80	76	74			72
8	87	79	75	71		86	79	74	71		78	74	71			77	73	71			69
9	84	76	71	68		83	76	71	68		75	71	68			74	70	68			66
10	81	73	69	65		80	73	68	65		72	68	65			72	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1655323
5°	1621169
10°	1436174
15°	1128563
20°	758787
25°	440809
30°	220325
35°	103888
40°	49098
45°	21528
50°	11148
55°	6280
60°	3564
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225057

CATALOG NUMBER: LSR2WM2B20FL408050D010 2LBD*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	381.5	20.9
10°-20°	763.3	41.8
20°-30°	482.5	26.5
30°-40°	150.9	8.3
40°-50°	35.0	1.9
50°-60°	9.2	0.5
60°-70°	1.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1627.3	89.2
0°-40°	1778.3	97.5
0°-60°	1822.5	99.9
0°-90°	1824.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1824.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4274	
5°	4169	381
15°	2814	763
25°	1031	483
35°	220	151
45°	39	35
55°	9	9
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225057

CATALOG NUMBER: LSR2WM2B20FL408050D010 2LBD*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4273.5
2.5°	4252.7
5°	4169.4
7.5°	3972.9
10°	3651.4
12.5°	3269.9
15°	2814.3
17.5°	2317.1
20°	1840.8
22.5°	1401.4
25°	1031.4
27.5°	728.4
30°	492.6
32.5°	328.4
35°	219.7
37.5°	148.0
40°	97.1
42.5°	60.1
45°	39.3
47.5°	27.8
50°	18.5
52.5°	13.9
55°	9.3
57.5°	6.9
60°	4.6
62.5°	4.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)