

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225156

Luminaire Tested: **LSR2WM2B20FL409024D010 2LBD*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225156
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL409024D010 2LBD*GPH
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1347.0 lumens
Efficiency: N/A
Efficacy: 64.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225156

CATALOG NUMBER: LSR2WM2B20FL409024D010 2LBD*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P225156

CATALOG NUMBER: LSR2WM2B20FL409024D010 2LBD*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	100		108	104	101	98		101	99	96		98	96	94		95	94	92
3	106	100	96	93		104	99	95	92		96	93	91		94	92	89		92	90	88
4	102	95	91	87		100	94	90	87		92	89	86		90	87	85		89	86	84
5	98	91	86	83		96	90	85	82		88	84	81		87	83	81		85	82	80
6	94	87	82	78		93	86	81	78		85	81	78		83	80	77		82	79	77
7	91	83	78	75		89	82	78	74		81	77	74		80	76	74		79	76	73
8	87	80	75	71		86	79	74	71		78	74	71		77	73	71		76	73	70
9	84	76	72	68		83	76	71	68		75	71	68		74	70	68		73	70	68
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1221960
5°	1197233
10°	1063816
15°	834662
20°	561341
25°	326611
30°	163611
35°	76320
40°	35597
45°	15064
50°	7231
55°	4660
60°	2634
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225156

CATALOG NUMBER: LSR2WM2B20FL409024D010 2LBD*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	281.9	20.9
10°-20°	565.0	41.9
20°-30°	357.2	26.5
30°-40°	111.1	8.2
40°-50°	24.7	1.8
50°-60°	6.3	0.5
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1204.1	89.4
0°-40°	1315.2	97.6
0°-60°	1346.2	99.9
0°-90°	1347.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1347.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3155	
5°	3079	282
15°	2081	565
25°	764	357
35°	161	111
45°	28	25
55°	7	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225156

CATALOG NUMBER: LSR2WM2B20FL409024D010 2LBD*GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3154.7
2.5°	3140.9
5°	3079.1
7.5°	2933.1
10°	2704.7
12.5°	2416.2
15°	2081.4
17.5°	1719.0
20°	1361.8
22.5°	1040.7
25°	764.2
27.5°	535.8
30°	365.8
32.5°	242.1
35°	161.4
37.5°	108.2
40°	70.4
42.5°	42.9
45°	27.5
47.5°	18.9
50°	12.0
52.5°	8.6
55°	6.9
57.5°	5.2
60°	3.4
62.5°	1.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)