

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2WM2B20WFL558050D010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29157)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20WFL558050D010 2LBD*H
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1838.8 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL558050D010 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL558050D010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	86	100	94	90	86	92	88	84		89	86	83		87
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	71	67	76	71	67		74	70	66		73
7	83	73	67	63	81	73	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	62	56	52	70	61	55	52	60	55	52		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	891670
5°	880457
10°	810832
15°	713638
20°	611176
25°	515602
30°	402586
35°	278138
40°	178644
45°	109120
50°	64539
55°	36805
60°	11620
65°	1741
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL558050D010 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.8	11.4
10°-20°	494.5	26.9
20°-30°	548.2	29.8
30°-40°	372.1	20.2
40°-50°	160.6	8.7
50°-60°	50.4	2.7
60°-70°	3.2	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1252.5	68.1
0°-40°	1624.6	88.3
0°-60°	1835.6	99.8
0°-90°	1838.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1838.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2302	
5°	2264	210
15°	1780	494
25°	1206	548
35°	588	372
45°	199	161
55°	54	50
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL558050D010 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2302.0
1°	2296.4
2°	2288.8
3°	2285.1
4°	2277.6
5°	2264.4
6°	2243.7
7°	2211.8
8°	2168.6
9°	2117.8
10°	2061.5
11°	2005.1
12°	1948.7
13°	1892.3
14°	1836.0
15°	1779.6
17.5°	1627.4
20°	1482.7
22.5°	1345.5
25°	1206.4
27.5°	1061.7
30°	900.1
32.5°	736.6
35°	588.2
37.5°	460.4
40°	353.3
42.5°	266.8
45°	199.2
47.5°	146.6
50°	107.1
52.5°	77.0
55°	54.5
57.5°	35.7
60°	15.0
62.5°	3.8
65°	1.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL558050D010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)