

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B20WFL559050D010 2LBD\*WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14804)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B20WFL559050D010 2LBD\*WH  
Description: 2000 Lumen, 2inch Portfolio LED Cylinder  
WIDE FLOOD OPTIC  
SPUN ROUND TRIM WITH WHEAT HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1533.5 lumens  
Efficiency: N/A  
Efficacy: 73.4 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.81  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559050D010 2LBD\*WH

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559050D010 2LBD\*WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 113 | 111 | 108 | 106 |  | 111 | 108 | 106 | 104 |  | 104 | 103 | 101 |  | 101 | 99  | 98  |  | 97  | 96  | 95  |
| 2   | 108 | 103 | 99  | 95  |  | 105 | 101 | 97  | 94  |  | 98  | 95  | 92  |  | 95  | 92  | 90  |  | 92  | 90  | 88  |
| 3   | 102 | 96  | 90  | 86  |  | 100 | 94  | 90  | 86  |  | 92  | 88  | 84  |  | 89  | 86  | 83  |  | 87  | 84  | 82  |
| 4   | 97  | 89  | 83  | 79  |  | 95  | 88  | 83  | 79  |  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 82  | 79  | 76  |
| 5   | 92  | 83  | 77  | 73  |  | 90  | 82  | 77  | 73  |  | 80  | 76  | 72  |  | 79  | 75  | 71  |  | 77  | 74  | 71  |
| 6   | 87  | 78  | 72  | 68  |  | 86  | 77  | 71  | 67  |  | 76  | 71  | 67  |  | 74  | 70  | 66  |  | 73  | 69  | 66  |
| 7   | 83  | 73  | 67  | 63  |  | 81  | 73  | 67  | 63  |  | 71  | 66  | 62  |  | 70  | 65  | 62  |  | 69  | 65  | 62  |
| 8   | 79  | 69  | 63  | 59  |  | 77  | 68  | 63  | 59  |  | 67  | 62  | 58  |  | 66  | 61  | 58  |  | 65  | 61  | 58  |
| 9   | 75  | 65  | 59  | 55  |  | 74  | 64  | 59  | 55  |  | 64  | 58  | 55  |  | 63  | 58  | 54  |  | 62  | 57  | 54  |
| 10  | 71  | 61  | 56  | 52  |  | 70  | 61  | 55  | 52  |  | 60  | 55  | 51  |  | 59  | 55  | 51  |  | 59  | 54  | 51  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 767642 |
| 5°  | 741102 |
| 10° | 670967 |
| 15° | 587801 |
| 20° | 506105 |
| 25° | 430253 |
| 30° | 338180 |
| 35° | 235012 |
| 40° | 152300 |
| 45° | 91152  |
| 50° | 53330  |
| 55° | 29849  |
| 60° | 11388  |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559050D010 2LBD\*WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 175.5  | 11.4      |
| 10°-20°   | 408.1  | 26.6      |
| 20°-30°   | 457.2  | 29.8      |
| 30°-40°   | 314.2  | 20.5      |
| 40°-50°   | 135.0  | 8.8       |
| 50°-60°   | 41.2   | 2.7       |
| 60°-70°   | 2.3    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1040.8 | 67.9      |
| 0°-40°    | 1355.0 | 88.4      |
| 0°-60°    | 1531.2 | 99.9      |
| 0°-90°    | 1533.5 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1533.5 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1982 |      |
| 5°  | 1906 | 175  |
| 15° | 1466 | 408  |
| 25° | 1007 | 457  |
| 35° | 497  | 314  |
| 45° | 166  | 135  |
| 55° | 44   | 41   |
| 65° | 0    | 2    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559050D010 2LBD\*WH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1981.8 |
| 2.5°  | 1960.7 |
| 5°    | 1906.0 |
| 7.5°  | 1817.5 |
| 10°   | 1705.9 |
| 12.5° | 1588.0 |
| 15°   | 1465.8 |
| 17.5° | 1337.4 |
| 20°   | 1227.8 |
| 22.5° | 1118.3 |
| 25°   | 1006.7 |
| 27.5° | 888.8  |
| 30°   | 756.1  |
| 32.5° | 621.3  |
| 35°   | 497.0  |
| 37.5° | 389.6  |
| 40°   | 301.2  |
| 42.5° | 225.3  |
| 45°   | 166.4  |
| 47.5° | 122.2  |
| 50°   | 88.5   |
| 52.5° | 61.1   |
| 55°   | 44.2   |
| 57.5° | 29.5   |
| 60°   | 14.7   |
| 62.5° | 2.1    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)