

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225466

Luminaire Tested: **LSR2WM2B20FL408027D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225466
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL408027D010 2LBDLC*MB
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1669.2 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225466

CATALOG NUMBER: LSR2WM2B20FL408027D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225466

CATALOG NUMBER: LSR2WM2B20FL408027D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90		
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	86		
4	101	94	90	86	99	93	89	86	91	87	85	89	86	84	88	85	83	81		
5	97	90	85	81	95	89	84	81	87	83	80	85	82	79	84	81	79	77		
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	77	75	74		
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	78	74	72	70		
8	86	78	73	69	85	77	73	69	76	72	69	75	72	69	75	71	68	67		
9	83	75	70	66	82	74	69	66	73	69	66	72	69	66	72	68	65	64		
10	80	72	67	63	79	71	66	63	70	66	63	70	66	63	69	65	63	62		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1451463
5°	1399461
10°	1230821
15°	964710
20°	668226
25°	411661
30°	229091
35°	122188
40°	60576
45°	30895
50°	16993
55°	11075
60°	5423
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225466

CATALOG NUMBER: LSR2WM2B20FL408027D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.3	19.7
10°-20°	657.1	39.4
20°-30°	448.9	26.9
30°-40°	171.1	10.3
40°-50°	47.5	2.8
50°-60°	14.8	0.9
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1434.3	85.9
0°-40°	1605.4	96.2
0°-60°	1667.8	99.9
0°-90°	1669.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1669.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3747	
5°	3599	328
15°	2406	657
25°	963	449
35°	258	171
45°	56	48
55°	16	15
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225466

CATALOG NUMBER: LSR2WM2B20FL408027D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3747.2
2.5°	3707.3
5°	3599.2
7.5°	3397.2
10°	3129.3
12.5°	2788.7
15°	2405.7
17.5°	2013.4
20°	1621.1
22.5°	1273.4
25°	963.2
27.5°	707.2
30°	512.2
32.5°	364.2
35°	258.4
37.5°	180.9
40°	119.8
42.5°	79.9
45°	56.4
47.5°	39.9
50°	28.2
52.5°	21.1
55°	16.4
57.5°	11.7
60°	7.0
62.5°	2.3
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)