

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225505

Luminaire Tested: **LSSQWM2B05FL409024D010 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225505
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14832)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL409024D010 2LBDL*H
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 516.0 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225505

CATALOG NUMBER: LSSQWM2B05FL409024D010 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P225505

CATALOG NUMBER: LSSQWM2B05FL409024D010 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95																
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90			90																
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86			86																
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82			82																
5	97	90	85	81	96	89	84	81	87	83	80	86	82	80	84	81	79	78			78																
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74			74																
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	75	72	71			71																
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68			68																
9	83	75	70	67	82	75	70	67	74	69	66	73	69	66	72	69	66	65			65																
10	80	72	67	64	79	72	67	64	71	67	64	70	66	64	70	66	63	62			62																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	453582
5°	438479
10°	386871
15°	304808
20°	209441
25°	126464
30°	68566
35°	35228
40°	17242
45°	8162
50°	4278
55°	2904
60°	1627
65°	642
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225505

CATALOG NUMBER: LSSQWM2B05FL409024D010 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.0	20.0
10°-20°	206.9	40.1
20°-30°	138.2	26.8
30°-40°	50.1	9.7
40°-50°	12.9	2.5
50°-60°	3.9	0.7
60°-70°	0.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	448.2	86.9
0°-40°	498.2	96.6
0°-60°	515.0	99.8
0°-90°	516.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	516.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1171	
5°	1128	103
15°	760	207
25°	296	138
35°	74	50
45°	15	13
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225505

CATALOG NUMBER: LSSQWM2B05FL409024D010 2LBDL*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1171.0
2.5°	1160.4
5°	1127.7
7.5°	1068.1
10°	983.6
12.5°	880.0
15°	760.1
17.5°	632.3
20°	508.1
22.5°	393.9
25°	295.9
27.5°	215.7
30°	153.3
32.5°	107.9
35°	74.5
37.5°	51.8
40°	34.1
42.5°	22.0
45°	14.9
47.5°	10.6
50°	7.1
52.5°	5.7
55°	4.3
57.5°	2.8
60°	2.1
62.5°	1.4
65°	0.7
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)