

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224892

Luminaire Tested: **LSR2B05FL408027D010 2LBD*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B05FL408027D010 2LBD*B
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 741.0 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224892

CATALOG NUMBER: LSR2B05FL408027D010 2LBD*B

Luminous Intensity Polar Plot





TEST NUMBER: P224892

CATALOG NUMBER: LSR2B05FL408027D010 2LBD*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																											
2	110	106	103	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91																											
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87																											
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83																											
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79																											
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76																											
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72																											
8	87	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	69																											
9	84	77	72	69	83	76	72	68	75	71	68	74	71	68	74	70	68	67																											
10	82	74	69	66	81	73	69	66	73	68	65	72	68	65	71	68	65	64																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	670457
5°	658787
10°	587701
15°	464530
20°	309731
25°	179717
30°	89946
35°	42321
40°	16535
45°	7395
50°	3495
55°	1958
60°	775
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224892

CATALOG NUMBER: LSR2B05FL408027D010 2LBD*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.3	21.0
10°-20°	313.6	42.3
20°-30°	197.2	26.6
30°-40°	60.3	8.1
40°-50°	11.9	1.6
50°-60°	2.7	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	666.1	89.9
0°-40°	726.4	98.0
0°-60°	740.9	100.0
0°-90°	741.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	741.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1731	
5°	1694	155
15°	1158	314
25°	420	197
35°	90	60
45°	14	12
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224892

CATALOG NUMBER: LSR2B05FL408027D010 2LBD*B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1730.9
2.5°	1727.0
5°	1694.3
7.5°	1617.4
10°	1494.2
12.5°	1340.3
15°	1158.4
17.5°	956.4
20°	751.4
22.5°	576.3
25°	420.5
27.5°	296.3
30°	201.1
32.5°	135.7
35°	89.5
37.5°	54.8
40°	32.7
42.5°	21.2
45°	13.5
47.5°	8.7
50°	5.8
52.5°	3.8
55°	2.9
57.5°	1.9
60°	1.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)