

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224934

Luminaire Tested: **LSR2B05FL408027D010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224934
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B05FL408027D010 2LBD*H
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 751.0 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224934

CATALOG NUMBER: LSR2B05FL408027D010 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224934

CATALOG NUMBER: LSR2B05FL408027D010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95					95			
2	110	106	103	100	108	104	101	99	101	99	97	98	96	94	96	94	93	91					91			
3	106	100	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87					87			
4	102	96	91	88	100	94	90	87	92	89	86	91	88	85	89	86	84	83					83			
5	98	91	86	83	96	90	86	82	89	85	82	87	84	81	86	83	80	79					79			
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76					76			
7	91	83	78	75	90	83	78	75	82	77	74	80	77	74	79	76	74	73					73			
8	88	80	75	72	87	79	75	72	78	74	71	77	74	71	77	73	71	70					70			
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67					67			
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64					64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	696564
5°	682000
10°	600641
15°	471227
20°	312946
25°	179632
30°	90080
35°	41612
40°	16939
45°	7560
50°	3917
55°	2431
60°	1162
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224934

CATALOG NUMBER: LSR2B05FL408027D010 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.2	21.3
10°-20°	318.1	42.4
20°-30°	197.6	26.3
30°-40°	59.6	7.9
40°-50°	12.2	1.6
50°-60°	3.1	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	675.9	90.0
0°-40°	735.5	97.9
0°-60°	750.8	100.0
0°-90°	751.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	751.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1798	
5°	1754	160
15°	1175	318
25°	420	198
35°	88	60
45°	14	12
55°	4	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224934

CATALOG NUMBER: LSR2B05FL408027D010 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1798.3
1°	1792.5
2°	1784.5
3°	1778.7
4°	1770.0
5°	1754.0
6°	1728.5
7°	1693.6
8°	1643.5
9°	1586.7
10°	1527.1
11°	1463.8
12°	1397.7
13°	1328.6
14°	1253.0
15°	1175.1
17.5°	966.4
20°	759.2
22.5°	575.9
25°	420.3
27.5°	296.7
30°	201.4
32.5°	132.3
35°	88.0
37.5°	54.5
40°	33.5
42.5°	21.8
45°	13.8
47.5°	8.7
50°	6.5
52.5°	4.4
55°	3.6
57.5°	2.2
60°	1.5
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224934

CATALOG NUMBER: LSR2B05FL408027D010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)