

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQ2B05WFL558027D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B05WFL558027D010 2LBDL*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 662.0 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSSQ2B05WFL558027D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL558027D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93		
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86		
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80		
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74		
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69		
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64		
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60		
8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56		
9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	53		
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	310535
5°	308572
10°	286849
15°	251834
20°	217067
25°	185615
30°	147330
35°	102706
40°	64975
45°	39660
50°	23441
55°	12831
60°	2789
65°	2475
70°	2039
75°	2694
80°	2008
85°	4000



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL558027D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.6	11.1
10°-20°	174.9	26.4
20°-30°	197.3	29.8
30°-40°	136.5	20.6
40°-50°	58.2	8.8
50°-60°	16.8	2.5
60°-70°	2.4	0.4
70°-80°	1.5	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	445.9	67.4
0°-40°	582.4	88.0
0°-60°	657.4	99.3
0°-90°	662.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	662.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	802	
5°	794	74
15°	628	175
25°	434	197
35°	217	137
45°	72	58
55°	19	17
65°	3	2
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL558027D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	801.7
2.5°	800.8
5°	793.6
7.5°	769.1
10°	729.3
12.5°	680.5
15°	628.0
17.5°	573.7
20°	526.6
22.5°	482.3
25°	434.3
27.5°	383.7
30°	329.4
32.5°	270.6
35°	217.2
37.5°	168.3
40°	128.5
42.5°	96.8
45°	72.4
47.5°	52.5
50°	38.9
52.5°	28.1
55°	19.0
57.5°	8.1
60°	3.6
62.5°	2.7
65°	2.7
67.5°	1.8
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)