

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225342

Luminaire Tested: **LSR2B05FL409027D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225342
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B05FL409027D010 2LBDC*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 518.0 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225342

CATALOG NUMBER: LSR2B05FL409027D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P225342

CATALOG NUMBER: LSR2B05FL409027D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																											
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91																											
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86																											
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82																											
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79																											
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75																											
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72																											
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69																											
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66																											
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	468960
5°	460408
10°	409290
15°	321891
20°	214182
25°	122960
30°	62126
35°	29223
40°	11782
45°	5807
50°	3194
55°	2229
60°	2092
65°	1192
70°	1472
75°	1048
80°	1561
85°	0



TEST NUMBER: P225342

CATALOG NUMBER: LSR2B05FL409027D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.4	20.9
10°-20°	217.4	42.0
20°-30°	135.3	26.1
30°-40°	41.6	8.0
40°-50°	9.1	1.8
50°-60°	3.3	0.6
60°-70°	1.6	0.3
70°-80°	1.0	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	461.1	89.0
0°-40°	502.7	97.0
0°-60°	515.1	99.4
0°-90°	518.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	518.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1211	
5°	1184	108
15°	803	217
25°	288	135
35°	62	42
45°	11	9
55°	3	3
65°	1	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P225342

CATALOG NUMBER: LSR2B05FL409027D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1210.7
2.5°	1205.4
5°	1184.1
7.5°	1130.3
10°	1040.6
12.5°	932.9
15°	802.7
17.5°	660.5
20°	519.6
22.5°	394.0
25°	287.7
27.5°	202.7
30°	138.9
32.5°	93.7
35°	61.8
37.5°	37.2
40°	23.3
42.5°	15.9
45°	10.6
47.5°	7.3
50°	5.3
52.5°	4.7
55°	3.3
57.5°	2.7
60°	2.7
62.5°	2.0
65°	1.3
67.5°	1.3
70°	1.3
72.5°	1.3
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)