

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQ2B20FL409027D010 2LBD*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B20FL409027D010 2LBD*LI
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1446.3 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSSQ2B20FL409027D010 2LBD*LI

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B20FL409027D010 2LBD*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1387357
5°	1333244
10°	1160574
15°	906283
20°	602726
25°	345117
30°	171572
35°	78873
40°	31603
45°	14462
50°	6689
55°	3782
60°	2169
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B20FL409027D010 2LBD*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	312.1	21.6
10°-20°	612.8	42.4
20°-30°	379.3	26.2
30°-40°	113.5	7.8
40°-50°	22.7	1.6
50°-60°	5.5	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1304.2	90.2
0°-40°	1417.7	98.0
0°-60°	1446.0	100.0
0°-90°	1446.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1446.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3582	
5°	3429	312
15°	2260	613
25°	808	379
35°	167	114
45°	26	23
55°	6	6
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B20FL409027D010 2LBD*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3581.7
1°	3562.3
2°	3544.2
3°	3508.1
4°	3474.7
5°	3428.9
6°	3366.3
7°	3287.1
8°	3185.6
9°	3070.3
10°	2950.7
11°	2827.0
12°	2695.0
13°	2557.4
14°	2410.1
15°	2260.0
17.5°	1863.8
20°	1462.2
22.5°	1106.4
25°	807.5
27.5°	567.1
30°	383.6
32.5°	253.0
35°	166.8
37.5°	104.2
40°	62.5
42.5°	40.3
45°	26.4
47.5°	16.7
50°	11.1
52.5°	8.3
55°	5.6
57.5°	4.2
60°	2.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B20FL409027D010 2LBD*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)