

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225472

Luminaire Tested: **LSSQWM2B20FL409027D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225472
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20FL409027D010 2LBDLC*MB
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1315.6 lumens
Efficiency: N/A
Efficacy: 62.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225472

CATALOG NUMBER: LSSQWM2B20FL409027D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225472

CATALOG NUMBER: LSSQWM2B20FL409027D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90				90
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	86				86
4	101	94	90	86	99	93	89	86	91	87	85	89	86	84	88	85	83	81				81
5	97	90	85	81	95	89	84	81	87	83	80	85	82	79	84	81	79	77				77
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	77	75	74				74
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	78	74	72	70				70
8	86	78	73	69	85	77	73	69	76	72	69	75	72	69	75	71	68	67				67
9	83	75	70	66	82	74	69	66	73	69	66	72	69	66	72	68	65	64				64
10	80	72	67	63	79	71	66	63	70	66	63	70	66	63	69	65	63	62				62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1143910
5°	1102904
10°	970009
15°	760315
20°	526633
25°	324431
30°	180518
35°	96322
40°	47733
45°	24322
50°	13378
55°	8779
60°	4338
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225472

CATALOG NUMBER: LSSQWM2B20FL409027D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.7	19.7
10°-20°	517.9	39.4
20°-30°	353.8	26.9
30°-40°	134.9	10.3
40°-50°	37.5	2.8
50°-60°	11.7	0.9
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1130.4	85.9
0°-40°	1265.2	96.2
0°-60°	1314.4	99.9
0°-90°	1315.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1315.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2953	
5°	2836	259
15°	1896	518
25°	759	354
35°	204	135
45°	44	37
55°	13	12
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225472

CATALOG NUMBER: LSSQWM2B20FL409027D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2953.2
2.5°	2921.7
5°	2836.5
7.5°	2677.3
10°	2466.2
12.5°	2197.8
15°	1896.0
17.5°	1586.8
20°	1277.6
22.5°	1003.5
25°	759.1
27.5°	557.3
30°	403.6
32.5°	287.0
35°	203.7
37.5°	142.6
40°	94.4
42.5°	63.0
45°	44.4
47.5°	31.5
50°	22.2
52.5°	16.7
55°	13.0
57.5°	9.3
60°	5.6
62.5°	1.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)