

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225162

Luminaire Tested: **LSSQ2B20FL409727D010 2LBD*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225162
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B20FL409727D010 2LBD*GPH
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1305.8 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225162

CATALOG NUMBER: LSSQ2B20FL409727D010 2LBD*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P225162

CATALOG NUMBER: LSSQ2B20FL409727D010 2LBD*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	99	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	96	93	91	94	92	89	92	90	88	87		
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83		
5	98	91	86	83	96	90	85	82	88	84	81	87	83	81	85	82	80	79		
6	94	87	82	78	93	86	81	78	85	81	78	83	80	77	82	79	77	75		
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72		
8	87	80	75	71	86	79	74	71	78	74	71	77	73	71	76	73	70	69		
9	84	76	72	68	83	76	71	68	75	71	68	74	70	68	73	70	68	66		
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1184582
5°	1160605
10°	1031289
15°	809118
20°	544193
25°	316610
30°	158601
35°	74003
40°	34536
45°	14571
50°	7050
55°	4525
60°	2556
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225162

CATALOG NUMBER: LSSQ2B20FL409727D010 2LBD*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.2	20.9
10°-20°	547.7	41.9
20°-30°	346.3	26.5
30°-40°	107.7	8.3
40°-50°	23.9	1.8
50°-60°	6.1	0.5
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1167.2	89.4
0°-40°	1275.0	97.6
0°-60°	1305.0	99.9
0°-90°	1305.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1305.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3058	
5°	2985	273
15°	2018	548
25°	741	346
35°	156	108
45°	27	24
55°	7	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225162

CATALOG NUMBER: LSSQ2B20FL409727D010 2LBD*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3058.2
2.5°	3044.9
5°	2984.9
7.5°	2843.4
10°	2622.0
12.5°	2342.3
15°	2017.7
17.5°	1666.4
20°	1320.2
22.5°	1008.8
25°	740.8
27.5°	519.4
30°	354.6
32.5°	234.7
35°	156.5
37.5°	104.9
40°	68.3
42.5°	41.6
45°	26.6
47.5°	18.3
50°	11.7
52.5°	8.3
55°	6.7
57.5°	5.0
60°	3.3
62.5°	1.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)