

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223676

Luminaire Tested: **LSSQWM2B05SP159727D010 2LBD\*WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223676  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA ( 150)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B05SP159727D010 2LBD\*WMH  
Description: 500 Lumen, 2inch Portfolio LED Cylinder  
SPOT OPTIC  
SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 297.0 lumens  
Efficiency: N/A  
Efficacy: 40.7 lumens/watt  
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223676

CATALOG NUMBER: LSSQWM2B05SP159727D010 2LBD\*WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P223676

CATALOG NUMBER: LSSQWM2B05SP159727D010 2LBD\*WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98	98	98	98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96	96	96	96
3	110	106	103	101	108	105	102	100	102	100	98	100	99	97	98	97	96	94	94	94	94
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93	93	93	93
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	96	94	92	91	91	91	91
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90	90	90	90
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88	88	88	88
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87	87	87	87
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86	86	86	86
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85	85	85	85

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1427138
5°	1031671
10°	300340
15°	105385
20°	45136
25°	20301
30°	7872
35°	3925
40°	2629
45°	1698
50°	904
55°	675
60°	387
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223676

CATALOG NUMBER: LSSQWM2B05SP159727D010 2LBD\*WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.8	63.2
10°-20°	76.4	25.7
20°-30°	23.4	7.9
30°-40°	5.8	2.0
40°-50°	2.4	0.8
50°-60°	1.0	0.3
60°-70°	0.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	287.6	96.8
0°-40°	293.4	98.8
0°-60°	296.8	99.9
0°-90°	297.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	297.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3684	
5°	2653	188
15°	263	76
25°	48	23
35°	8	6
45°	3	2
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223676

CATALOG NUMBER: LSSQWM2B05SP159727D010 2LBD\*WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3684.4
1°	3628.1
2°	3490.8
3°	3271.9
4°	2985.8
5°	2653.3
6°	2278.5
7°	1871.6
8°	1459.1
9°	1073.4
10°	763.6
11°	547.3
12°	411.5
13°	335.1
14°	293.3
15°	262.8
17.5°	162.1
20°	109.5
22.5°	73.3
25°	47.5
27.5°	28.9
30°	17.6
32.5°	11.4
35°	8.3
37.5°	6.7
40°	5.2
42.5°	4.1
45°	3.1
47.5°	2.1
50°	1.5
52.5°	1.5
55°	1.0
57.5°	1.0
60°	0.5
62.5°	0.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223676

CATALOG NUMBER: LSSQWM2B05SP159727D010 2LBD\*WMH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)