

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224134

Luminaire Tested: **LSR2B05SP158030D010 2LBD\*LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224134  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA ( 150)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2B05SP158030D010 2LBD\*LI  
Description: 500 Lumen, 2inch Portfolio LED Cylinder  
SPOT OPTIC  
SPUN ROUND TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 427.0 lumens  
Efficiency: N/A  
Efficacy: 58.5 lumens/watt  
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224134

CATALOG NUMBER: LSR2B05SP158030D010 2LBD\*LI

### Luminous Intensity Polar Plot





TEST NUMBER: P224134

CATALOG NUMBER: LSR2B05SP158030D010 2LBD\*LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |     |    |    |   |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|-----|----|----|---|--|--|--|--|--|--|---|--|--|--|--|--|--|--|--|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |    |    |    |    |    |    |     | 20 |    |   |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |    |    |    |    |    |    |     | 10 |    |   |  |  |  |  |  |  | 0 |  |  |  |  |  |  |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50  | 30 | 10 | 0 |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |     |    |    |   |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    |    |    |    |    |    | 100 |    |    |   |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 1   | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 106 | 104 | 103 | 103 | 101 | 100 | 100 | 98  |    |    |    |    |    |    |    |    | 98  |    |    |   |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 2   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 104 | 105 | 103 | 102 | 102 | 101 | 100 | 100 | 99  | 98  | 96  |    |    |    |    |    |    |    |    | 96  |    |    |   |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 3   | 110 | 106 | 103 | 101 | 108 | 105 | 102 | 100 | 102 | 100 | 98  | 100 | 99  | 97  | 98  | 97  | 96  | 94  |    |    |    |    |    |    |    |    | 94  |    |    |   |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 4   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 97  | 100 | 98  | 96  | 98  | 96  | 95  | 97  | 95  | 94  | 91  |    |    |    |    |    |    |    |    | 91  |    |    |   |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 5   | 105 | 101 | 97  | 95  | 104 | 100 | 97  | 94  | 98  | 96  | 94  | 97  | 95  | 93  | 95  | 94  | 92  | 89  |    |    |    |    |    |    |    |    | 89  |    |    |   |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 6   | 103 | 98  | 95  | 93  | 102 | 98  | 95  | 92  | 96  | 94  | 92  | 95  | 93  | 91  | 94  | 92  | 91  | 88  |    |    |    |    |    |    |    |    | 88  |    |    |   |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 7   | 101 | 96  | 93  | 91  | 100 | 96  | 93  | 90  | 95  | 92  | 90  | 94  | 91  | 90  | 93  | 91  | 89  | 86  |    |    |    |    |    |    |    |    | 86  |    |    |   |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 8   | 100 | 94  | 91  | 89  | 99  | 94  | 91  | 89  | 93  | 90  | 89  | 92  | 90  | 88  | 92  | 90  | 88  | 85  |    |    |    |    |    |    |    |    | 85  |    |    |   |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 9   | 98  | 93  | 90  | 88  | 97  | 92  | 89  | 87  | 92  | 89  | 87  | 91  | 89  | 87  | 90  | 88  | 87  | 84  |    |    |    |    |    |    |    |    | 84  |    |    |   |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 10  | 96  | 91  | 88  | 86  | 96  | 91  | 88  | 86  | 90  | 88  | 86  | 90  | 87  | 86  | 89  | 87  | 86  | 83  |    |    |    |    |    |    |    |    | 83  |    |    |   |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2051810 |
| 5°  | 1483253 |
| 10° | 431828  |
| 15° | 151502  |
| 20° | 64881   |
| 25° | 29191   |
| 30° | 11271   |
| 35° | 5627    |
| 40° | 3742    |
| 45° | 2465    |
| 50° | 1326    |
| 55° | 1013    |
| 60° | 542     |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P224134

CATALOG NUMBER: LSR2B05SP158030D010 2LBD\*LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 269.9  | 63.2      |
| 10°-20°   | 109.8  | 25.7      |
| 20°-30°   | 33.7   | 7.9       |
| 30°-40°   | 8.3    | 1.9       |
| 40°-50°   | 3.5    | 0.8       |
| 50°-60°   | 1.5    | 0.3       |
| 60°-70°   | 0.3    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 413.5  | 96.8      |
| 0°-40°    | 421.8  | 98.8      |
| 0°-60°    | 426.7  | 99.9      |
| 0°-90°    | 427.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 427.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5297 |      |
| 5°  | 3815 | 270  |
| 15° | 378  | 110  |
| 25° | 68   | 34   |
| 35° | 12   | 8    |
| 45° | 4    | 3    |
| 55° | 2    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P224134

CATALOG NUMBER: LSR2B05SP158030D010 2LBD\*LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 5297.1 |
| 1°    | 5216.2 |
| 2°    | 5018.8 |
| 3°    | 4704.0 |
| 4°    | 4292.8 |
| 5°    | 3814.7 |
| 6°    | 3275.8 |
| 7°    | 2690.9 |
| 8°    | 2097.8 |
| 9°    | 1543.3 |
| 10°   | 1097.9 |
| 11°   | 786.8  |
| 12°   | 591.6  |
| 13°   | 481.8  |
| 14°   | 421.6  |
| 15°   | 377.8  |
| 17.5° | 233.1  |
| 20°   | 157.4  |
| 22.5° | 105.4  |
| 25°   | 68.3   |
| 27.5° | 41.6   |
| 30°   | 25.2   |
| 32.5° | 16.3   |
| 35°   | 11.9   |
| 37.5° | 9.7    |
| 40°   | 7.4    |
| 42.5° | 5.9    |
| 45°   | 4.5    |
| 47.5° | 3.0    |
| 50°   | 2.2    |
| 52.5° | 2.2    |
| 55°   | 1.5    |
| 57.5° | 1.5    |
| 60°   | 0.7    |
| 62.5° | 0.7    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P224134

CATALOG NUMBER: LSR2B05SP158030D010 2LBD\*LI

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |  |     |
|-------|--|-----|
| 85°   |  | 0.0 |
| 87.5° |  | 0.0 |



(END OF REPORT)