

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B20WFL559727D010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29157)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20WFL559727D010 2LBD*H
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1223.4 lumens
Efficiency: N/A
Efficacy: 58.5 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559727D010 2LBD*H

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559727D010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93						
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87						
3	102	96	91	86	100	94	90	86	92	88	84	89	86	83	87	84	82	80						
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74						
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69						
6	87	78	72	68	86	77	71	67	76	71	67	74	70	66	73	69	66	64						
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60						
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56						
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53						
10	71	62	56	52	70	61	55	52	60	55	52	59	55	51	59	54	51	50						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	593259
5°	585805
10°	539440
15°	474796
20°	406640
25°	343065
30°	267869
35°	185031
40°	118826
45°	72582
50°	42966
55°	24514
60°	7747
65°	1192
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559727D010 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.6	11.4
10°-20°	329.0	26.9
20°-30°	364.8	29.8
30°-40°	247.5	20.2
40°-50°	106.8	8.7
50°-60°	33.6	2.7
60°-70°	2.1	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	833.3	68.1
0°-40°	1080.9	88.3
0°-60°	1221.3	99.8
0°-90°	1223.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1223.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1532	
5°	1507	140
15°	1184	329
25°	803	365
35°	391	248
45°	132	107
55°	36	34
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559727D010 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1531.6
1°	1527.8
2°	1522.8
3°	1520.3
4°	1515.3
5°	1506.6
6°	1492.8
7°	1471.6
8°	1442.8
9°	1409.0
10°	1371.5
11°	1334.0
12°	1296.5
13°	1259.0
14°	1221.5
15°	1184.0
17.5°	1082.7
20°	986.5
22.5°	895.2
25°	802.7
27.5°	706.4
30°	598.9
32.5°	490.1
35°	391.3
37.5°	306.3
40°	235.0
42.5°	177.5
45°	132.5
47.5°	97.5
50°	71.3
52.5°	51.3
55°	36.3
57.5°	23.8
60°	10.0
62.5°	2.5
65°	1.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559727D010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)