

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223406

Luminaire Tested: **LSR2WM2B20NFL258030D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20NFL258030D010 2LBDLC*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1734.6 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223406

CATALOG NUMBER: LSR2WM2B20NFL258030D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223406

CATALOG NUMBER: LSR2WM2B20NFL258030D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	112	110		113	111	110	108		107	106	105		104	103	102		100	100	99
2	112	109	106	104		110	107	104	102		104	102	100		101	99	98		98	97	96
3	109	105	101	99		107	103	100	98		101	98	96		99	97	95		96	95	93
4	106	101	97	95		104	100	97	94		98	95	93		96	94	92		95	93	91
5	103	98	94	91		102	97	94	91		95	92	90		94	91	89		93	90	89
6	101	95	91	89		99	94	91	88		93	90	88		92	89	87		91	88	87
7	98	92	89	86		97	92	88	86		91	88	85		90	87	85		89	86	85
8	96	90	86	84		95	90	86	84		89	86	83		88	85	83		87	85	83
9	94	88	84	82		93	88	84	82		87	84	82		86	83	81		85	83	81
10	92	86	82	80		91	86	82	80		85	82	80		84	82	80		84	81	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3986061
5°	3680429
10°	2491180
15°	847535
20°	311297
25°	165015
30°	84847
35°	39579
40°	12944
45°	6573
50°	3073
55°	1148
60°	1317
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223406

CATALOG NUMBER: LSR2WM2B20NFL258030D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	805.2	46.4
10°-20°	677.0	39.0
20°-30°	185.8	10.7
30°-40°	54.2	3.1
40°-50°	10.0	0.6
50°-60°	2.3	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1667.9	96.2
0°-40°	1722.1	99.3
0°-60°	1734.4	100.0
0°-90°	1734.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1734.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10291	
5°	9466	805
15°	2114	677
25°	386	186
35°	84	54
45°	12	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223406

CATALOG NUMBER: LSR2WM2B20NFL258030D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	10290.7
1°	10230.9
2°	10125.0
3°	9972.9
4°	9764.5
5°	9465.5
6°	9057.1
7°	8546.3
8°	7922.6
9°	7186.3
10°	6333.7
11°	5399.1
12°	4426.9
13°	3499.2
14°	2708.1
15°	2113.5
17.5°	1192.6
20°	755.2
22.5°	538.2
25°	386.1
27.5°	273.4
30°	189.7
32.5°	133.3
35°	83.7
37.5°	34.2
40°	25.6
42.5°	18.8
45°	12.0
47.5°	6.8
50°	5.1
52.5°	3.4
55°	1.7
57.5°	1.7
60°	1.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223406

CATALOG NUMBER: LSR2WM2B20NFL258030D010 2LBDLC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)