

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224842

Luminaire Tested: **LSSQWM2B20FL408030D010 2LBDL*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224842
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20FL408030D010 2LBDL*B
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1717.6 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224842

CATALOG NUMBER: LSSQWM2B20FL408030D010 2LBDL*B

Luminous Intensity Polar Plot





TEST NUMBER: P224842

CATALOG NUMBER: LSSQWM2B20FL408030D010 2LBDL*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			99
2	110	106	103	100	108	104	101	99		101	99	96			98	96	94			96
3	106	100	96	93	104	99	95	92		97	93	91			94	92	89			92
4	102	95	91	87	100	94	90	87		92	89	86			90	87	85			89
5	98	91	86	83	96	90	86	82		88	85	82			87	84	81			85
6	94	87	82	79	93	86	82	78		85	81	78			84	80	77			82
7	91	83	78	75	90	83	78	75		81	77	74			80	77	74			79
8	87	80	75	72	86	79	75	71		78	74	71			77	74	71			76
9	84	77	72	69	83	76	72	68		75	71	68			74	71	68			74
10	82	74	69	66	81	73	69	66		73	68	65			72	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1554071
5°	1527074
10°	1362269
15°	1076752
20°	717979
25°	416533
30°	208472
35°	98072
40°	38328
45°	17091
50°	8075
55°	4525
60°	1704
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224842

CATALOG NUMBER: LSSQWM2B20FL408030D010 2LBDL*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	360.0	21.0
10°-20°	726.8	42.3
20°-30°	457.2	26.6
30°-40°	139.8	8.1
40°-50°	27.4	1.6
50°-60°	6.2	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1544.0	89.9
0°-40°	1683.7	98.0
0°-60°	1717.3	100.0
0°-90°	1717.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1717.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4012	
5°	3927	360
15°	2685	727
25°	975	457
35°	207	140
45°	31	27
55°	7	6
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224842

CATALOG NUMBER: LSSQWM2B20FL408030D010 2LBDL*B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4012.1
2.5°	4003.2
5°	3927.4
7.5°	3748.9
10°	3463.5
12.5°	3106.7
15°	2685.1
17.5°	2216.8
20°	1741.8
22.5°	1335.9
25°	974.6
27.5°	686.9
30°	466.1
32.5°	314.5
35°	207.4
37.5°	127.1
40°	75.8
42.5°	49.1
45°	31.2
47.5°	20.1
50°	13.4
52.5°	8.9
55°	6.7
57.5°	4.5
60°	2.2
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)