

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223837

Luminaire Tested: **LSR2B05SP159030D010 2LBD\*WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223837  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA ( 150)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2B05SP159030D010 2LBD\*WH  
Description: 500 Lumen, 2inch Portfolio LED Cylinder  
SPOT OPTIC  
SPUN ROUND TRIM WITH WHEAT HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 345.0 lumens  
Efficiency: N/A  
Efficacy: 47.3 lumens/watt  
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223837

CATALOG NUMBER: LSR2B05SP159030D010 2LBD\*WH

### Luminous Intensity Polar Plot





TEST NUMBER: P223837

CATALOG NUMBER: LSR2B05SP159030D010 2LBD\*WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96																			
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	96	94																			
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93																			
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91																			
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90																			
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88																			
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87																			
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86																			
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1657802
5°	1198438
10°	348876
15°	122428
20°	52391
25°	23592
30°	9124
35°	4539
40°	3034
45°	1972
50°	1085
55°	810
60°	465
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223837

CATALOG NUMBER: LSR2B05SP159030D010 2LBD\*WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	218.1	63.2
10°-20°	88.7	25.7
20°-30°	27.2	7.9
30°-40°	6.7	1.9
40°-50°	2.8	0.8
50°-60°	1.2	0.3
60°-70°	0.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	334.1	96.8
0°-40°	340.8	98.8
0°-60°	344.8	99.9
0°-90°	345.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	345.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4280	
5°	3082	218
15°	305	89
25°	55	27
35°	10	7
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223837

CATALOG NUMBER: LSR2B05SP159030D010 2LBD\*WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4279.9
1°	4214.5
2°	4055.0
3°	3800.7
4°	3468.4
5°	3082.2
6°	2646.7
7°	2174.1
8°	1694.9
9°	1246.9
10°	887.0
11°	635.7
12°	478.0
13°	389.2
14°	340.7
15°	305.3
17.5°	188.3
20°	127.1
22.5°	85.2
25°	55.2
27.5°	33.6
30°	20.4
32.5°	13.2
35°	9.6
37.5°	7.8
40°	6.0
42.5°	4.8
45°	3.6
47.5°	2.4
50°	1.8
52.5°	1.8
55°	1.2
57.5°	1.2
60°	0.6
62.5°	0.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223837

CATALOG NUMBER: LSR2B05SP159030D010 2LBD\*WH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)