

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225318

Luminaire Tested: **LSR2WM2B20FL409030D010 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225318
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL409030D010 2LBDC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1504.5 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225318

CATALOG NUMBER: LSR2WM2B20FL409030D010 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P225318

CATALOG NUMBER: LSR2WM2B20FL409030D010 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	99		108	104	101	98		101	98	96		98	96	94		95	94	92
3	105	100	96	93		104	99	95	92		96	93	90		94	91	89		92	90	88
4	101	95	90	87		100	94	90	86		92	88	85		90	87	85		88	86	84
5	98	91	86	82		96	90	85	82		88	84	81		86	83	80		85	82	80
6	94	86	82	78		93	86	81	78		84	80	77		83	79	77		82	79	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	76	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1362025
5°	1337210
10°	1188735
15°	934915
20°	622100
25°	357169
30°	180428
35°	84879
40°	34131
45°	16927
50°	9280
55°	6483
60°	5965
65°	3575
70°	4417
75°	2844
80°	4238
85°	0



TEST NUMBER: P225318

CATALOG NUMBER: LSR2WM2B20FL409030D010 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.0	20.9
10°-20°	631.5	42.0
20°-30°	392.9	26.1
30°-40°	120.8	8.0
40°-50°	26.5	1.8
50°-60°	9.4	0.6
60°-70°	4.8	0.3
70°-80°	2.8	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1339.4	89.0
0°-40°	1460.2	97.1
0°-60°	1496.1	99.4
0°-90°	1504.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1504.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3516	
5°	3439	315
15°	2331	632
25°	836	393
35°	180	121
45°	31	27
55°	10	9
65°	4	5
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P225318

CATALOG NUMBER: LSR2WM2B20FL409030D010 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3516.3
2.5°	3500.9
5°	3439.1
7.5°	3282.8
10°	3022.3
12.5°	2709.6
15°	2331.4
17.5°	1918.4
20°	1509.2
22.5°	1144.5
25°	835.7
27.5°	588.6
30°	403.4
32.5°	272.1
35°	179.5
37.5°	108.1
40°	67.5
42.5°	46.3
45°	30.9
47.5°	21.2
50°	15.4
52.5°	13.5
55°	9.6
57.5°	7.7
60°	7.7
62.5°	5.8
65°	3.9
67.5°	3.9
70°	3.9
72.5°	3.9
75°	1.9
77.5°	1.9
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)