

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225285

Luminaire Tested: **LSRWM2B05FL409030D010 2LBDC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225285  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSRWM2B05FL409030D010 2LBDC\*MMS  
Description: 500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
CAST ROUND TRIM WITH MATTE METALLIC SILVER  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 621.0 lumens  
Efficiency: N/A  
Efficacy: 85.1 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225285

CATALOG NUMBER: LSRWM2B05FL409030D010 2LBDC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P225285

CATALOG NUMBER: LSRWM2B05FL409030D010 2LBDC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95																
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91																
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			86																
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			82																
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			79																
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75			75																
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			72																
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69																
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			66																
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	562194
5°	551938
10°	490668
15°	385892
20°	256762
25°	147406
30°	74470
35°	35039
40°	14107
45°	6957
50°	3857
55°	2701
60°	2479
65°	1466
70°	1812
75°	1197
80°	1785
85°	0



TEST NUMBER: P225285

CATALOG NUMBER: LSRWM2B05FL409030D010 2LBDC\*MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	130.0	20.9
10°-20°	260.7	42.0
20°-30°	162.2	26.1
30°-40°	49.9	8.0
40°-50°	11.0	1.8
50°-60°	3.9	0.6
60°-70°	2.0	0.3
70°-80°	1.2	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	552.8	89.0
0°-40°	602.7	97.0
0°-60°	617.6	99.4
0°-90°	621.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	621.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1451	
5°	1420	130
15°	962	261
25°	345	162
35°	74	50
45°	13	11
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P225285

CATALOG NUMBER: LSRWM2B05FL409030D010 2LBDC\*MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1451.4
2.5°	1445.0
5°	1419.5
7.5°	1355.0
10°	1247.5
12.5°	1118.4
15°	962.3
17.5°	791.8
20°	622.9
22.5°	472.4
25°	344.9
27.5°	243.0
30°	166.5
32.5°	112.3
35°	74.1
37.5°	44.6
40°	27.9
42.5°	19.1
45°	12.7
47.5°	8.8
50°	6.4
52.5°	5.6
55°	4.0
57.5°	3.2
60°	3.2
62.5°	2.4
65°	1.6
67.5°	1.6
70°	1.6
72.5°	1.6
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)