

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224521

Luminaire Tested: **LSR2WM2B20FL409030D010 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224521
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL409030D010 2LBDL*WMH
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1440.0 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224521

CATALOG NUMBER: LSR2WM2B20FL409030D010 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P224521

CATALOG NUMBER: LSR2WM2B20FL409030D010 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	100	108	104	101	98		101	98	96			98	96	94			91
3	106	100	96	93	104	99	95	92		96	93	91			94	91	89			87
4	102	95	91	87	100	94	90	87		92	89	86			90	87	85			82
5	98	91	86	82	96	90	85	82		88	84	81			87	83	81			79
6	94	87	82	78	93	86	81	78		85	81	77			83	80	77			75
7	91	83	78	75	89	82	78	74		81	77	74			80	76	74			72
8	87	79	75	71	86	79	74	71		78	74	71			77	73	71			69
9	84	76	71	68	83	76	71	68		75	71	68			74	70	68			66
10	81	73	69	65	80	73	68	65		72	68	65			72	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1306634
5°	1279703
10°	1133670
15°	890844
20°	598934
25°	347937
30°	173898
35°	81994
40°	38783
45°	16981
50°	8798
55°	4930
60°	2866
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224521

CATALOG NUMBER: LSR2WM2B20FL409030D010 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.1	20.9
10°-20°	602.5	41.8
20°-30°	380.9	26.5
30°-40°	119.1	8.3
40°-50°	27.7	1.9
50°-60°	7.3	0.5
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1284.5	89.2
0°-40°	1403.7	97.5
0°-60°	1438.6	99.9
0°-90°	1440.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1440.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3373	
5°	3291	301
15°	2222	603
25°	814	381
35°	173	119
45°	31	28
55°	7	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224521

CATALOG NUMBER: LSR2WM2B20FL409030D010 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3373.3
2.5°	3356.9
5°	3291.2
7.5°	3136.0
10°	2882.3
12.5°	2581.1
15°	2221.5
17.5°	1829.1
20°	1453.0
22.5°	1106.2
25°	814.1
27.5°	575.0
30°	388.8
32.5°	259.2
35°	173.4
37.5°	116.8
40°	76.7
42.5°	47.5
45°	31.0
47.5°	21.9
50°	14.6
52.5°	11.0
55°	7.3
57.5°	5.5
60°	3.7
62.5°	3.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)