

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSRWM2B05WFL559030D010 2LBDL*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14809)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B05WFL559030D010 2LBDL*B
Description: 500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 539.0 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSRWM2B05WFL559030D010 2LBDL*B

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B05WFL559030D010 2LBDL*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	63	70	66	62	69	65	62	60		
8	79	69	63	59	78	69	63	59	67	62	59	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53		
10	71	62	56	52	70	61	56	52	60	55	52	60	55	52	59	55	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	256578
5°	254953
10°	237448
15°	208245
20°	179886
25°	153005
30°	121344
35°	83744
40°	52587
45°	31388
50°	18138
55°	9184
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B05WFL559030D010 2LBDL*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.9	11.3
10°-20°	144.7	26.9
20°-30°	162.9	30.2
30°-40°	111.9	20.8
40°-50°	46.5	8.6
50°-60°	12.0	2.2
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	368.5	68.4
0°-40°	480.4	89.1
0°-60°	538.9	100.0
0°-90°	539.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	539.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	662	
5°	656	61
15°	519	145
25°	358	163
35°	177	112
45°	57	46
55°	14	12
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B05WFL559030D010 2LBDL*B

CANDELA DISTRIBUTION (FULL):

	0°
0°	662.4
2.5°	661.7
5°	655.7
7.5°	636.1
10°	603.7
12.5°	563.0
15°	519.3
17.5°	474.8
20°	436.4
22.5°	398.7
25°	358.0
27.5°	316.5
30°	271.3
32.5°	223.1
35°	177.1
37.5°	137.9
40°	104.0
42.5°	78.4
45°	57.3
47.5°	41.4
50°	30.1
52.5°	21.1
55°	13.6
57.5°	4.5
60°	0.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)