

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222264

Luminaire Tested: **LSR2B05NFL259730D010 2LBD*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222264
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B05NFL259730D010 2LBD*B
Description: 500 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
SPUN ROUND TRIM WITH BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 563.0 lumens
Efficiency: N/A
Efficacy: 77.1 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222264

CATALOG NUMBER: LSR2B05NFL259730D010 2LBD*B

Luminous Intensity Polar Plot





TEST NUMBER: P222264

CATALOG NUMBER: LSR2B05NFL259730D010 2LBD*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	97	97	97	96	96	96	95																
	1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	96	95	95	95	94	94	94	93																
	2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	95	94	93	93	93	92	92	92	91																
	3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	92	91	90	90	90	89	89	89	88																
	4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	90	89	88	88	87	87	87	86	86	86																
	5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	88	87	87	87	86	86	86	85	85	85																
	6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	86	86	85	85	85	84	84	84	84	84																
	7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84	84	84	83	83	83	82	82	82	82	82																
	8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	82	82	81	81	81	80	80	80	80	80																
	9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	80	80	79	79	79	78	78	78	78	78																
	10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	78	78	78	77	77	77	76	76	76	76	76																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1293774
5°	1194550
10°	808551
15°	275093
20°	101031
25°	53552
30°	27552
35°	12862
40°	4197
45°	2136
50°	1024
55°	405
60°	465
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222264

CATALOG NUMBER: LSR2B05NFL259730D010 2LBD*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.3	46.4
10°-20°	219.7	39.0
20°-30°	60.3	10.7
30°-40°	17.6	3.1
40°-50°	3.3	0.6
50°-60°	0.8	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	541.4	96.1
0°-40°	559.0	99.3
0°-60°	563.0	100.0
0°-90°	563.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	563.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3340	
5°	3072	261
15°	686	220
25°	125	60
35°	27	18
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222264

CATALOG NUMBER: LSR2B05NFL259730D010 2LBD*B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3340.1
1°	3320.7
2°	3286.3
3°	3236.9
4°	3169.3
5°	3072.2
6°	2939.7
7°	2773.9
8°	2571.5
9°	2332.4
10°	2055.7
11°	1752.4
12°	1436.8
13°	1135.7
14°	879.0
15°	686.0
17.5°	387.1
20°	245.1
22.5°	174.7
25°	125.3
27.5°	88.7
30°	61.6
32.5°	43.3
35°	27.2
37.5°	11.1
40°	8.3
42.5°	6.1
45°	3.9
47.5°	2.2
50°	1.7
52.5°	1.1
55°	0.6
57.5°	0.6
60°	0.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222264

CATALOG NUMBER: LSR2B05NFL259730D010 2LBD*B

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)