

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225081

Luminaire Tested: **LSSQ2B20FL409030D010 2LBD*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225081
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14829)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B20FL409030D010 2LBD*WH
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1523.8 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225081

CATALOG NUMBER: LSSQ2B20FL409030D010 2LBD*WH

Luminous Intensity Polar Plot





TEST NUMBER: P225081

CATALOG NUMBER: LSSQ2B20FL409030D010 2LBD*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95
3	106	100	96	93	104	99	95	92	96	93	91		94	91	89		92
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		88
5	98	91	86	82	96	90	85	82	88	84	81		87	83	81		85
6	94	87	82	78	93	86	81	78	85	80	77		83	80	77		82
7	91	83	78	75	89	82	78	74	81	77	74		80	76	74		79
8	87	79	75	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		71	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1405950
5°	1352763
10°	1190702
15°	935276
20°	635867
25°	371316
30°	189105
35°	89466
40°	39036
45°	16927
50°	8135
55°	5200
60°	3021
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225081

CATALOG NUMBER: LSSQ2B20FL409030D010 2LBD*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	317.7	20.9
10°-20°	634.2	41.6
20°-30°	407.1	26.7
30°-40°	129.2	8.5
40°-50°	27.6	1.8
50°-60°	7.1	0.5
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1359.0	89.2
0°-40°	1488.2	97.7
0°-60°	1522.9	99.9
0°-90°	1523.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1523.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3630	
5°	3479	318
15°	2332	634
25°	869	407
35°	189	129
45°	31	28
55°	8	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225081

CATALOG NUMBER: LSSQ2B20FL409030D010 2LBD*WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3629.7
2.5°	3595.0
5°	3479.1
7.5°	3289.9
10°	3027.3
12.5°	2706.8
15°	2332.3
17.5°	1932.6
20°	1542.6
22.5°	1177.7
25°	868.8
27.5°	619.8
30°	422.8
32.5°	283.8
35°	189.2
37.5°	125.5
40°	77.2
42.5°	48.3
45°	30.9
47.5°	21.2
50°	13.5
52.5°	9.7
55°	7.7
57.5°	5.8
60°	3.9
62.5°	1.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)