

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225425

Luminaire Tested: **LSSQ2B05FL409730D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225425
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B05FL409730D010 2LBDLC*MB
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 520.0 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225425

CATALOG NUMBER: LSSQ2B05FL409730D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225425

CATALOG NUMBER: LSSQ2B05FL409730D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	86	86	86	86
4	101	94	90	86	99	93	89	86	91	87	85	89	86	84	88	85	83	81	81	81	81
5	97	90	85	81	95	89	84	81	87	83	80	85	82	79	84	81	79	77	77	77	77
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	77	75	74	74	74	74
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	78	74	72	70	70	70	70
8	86	78	73	69	85	77	73	69	76	72	69	75	72	69	75	71	68	67	67	67	67
9	83	75	70	66	82	74	69	66	73	69	66	72	69	66	72	68	65	64	64	64	64
10	80	72	67	63	79	71	66	63	70	66	63	70	66	63	69	65	63	62	62	62	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	452188
5°	435990
10°	383449
15°	300557
20°	208164
25°	128259
30°	71384
35°	38065
40°	18861
45°	9641
50°	5303
55°	3444
60°	1704
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225425

CATALOG NUMBER: LSSQ2B05FL409730D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.3	19.7
10°-20°	204.7	39.4
20°-30°	139.9	26.9
30°-40°	53.3	10.3
40°-50°	14.8	2.8
50°-60°	4.6	0.9
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	446.8	85.9
0°-40°	500.1	96.2
0°-60°	519.6	99.9
0°-90°	520.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	520.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1167	
5°	1121	102
15°	750	205
25°	300	140
35°	80	53
45°	18	15
55°	5	5
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225425

CATALOG NUMBER: LSSQ2B05FL409730D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1167.4
2.5°	1154.9
5°	1121.3
7.5°	1058.3
10°	974.9
12.5°	868.7
15°	749.5
17.5°	627.2
20°	505.0
22.5°	396.7
25°	300.1
27.5°	220.3
30°	159.6
32.5°	113.4
35°	80.5
37.5°	56.4
40°	37.3
42.5°	24.9
45°	17.6
47.5°	12.4
50°	8.8
52.5°	6.6
55°	5.1
57.5°	3.7
60°	2.2
62.5°	0.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)