

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224759

Luminaire Tested: **LSSQWM2B05FL409730D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224759
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL409730D010 2LBDL*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 532.0 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224759

CATALOG NUMBER: LSSQWM2B05FL409730D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224759

CATALOG NUMBER: LSSQWM2B05FL409730D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91				91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86				86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82				82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79				79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75				75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72				72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69				69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66				66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64				64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	481626
5°	472851
10°	420343
15°	330593
20°	219994
25°	126293
30°	63781
35°	30027
40°	12085
45°	5971
50°	3314
55°	2296
60°	2092
65°	1283
70°	1586
75°	1048
80°	1561
85°	0



TEST NUMBER: P224759

CATALOG NUMBER: LSSQWM2B05FL409730D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.4	20.9
10°-20°	223.3	42.0
20°-30°	138.9	26.1
30°-40°	42.7	8.0
40°-50°	9.4	1.8
50°-60°	3.3	0.6
60°-70°	1.7	0.3
70°-80°	1.0	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	473.6	89.0
0°-40°	516.3	97.0
0°-60°	529.0	99.4
0°-90°	532.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	532.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1243	
5°	1216	111
15°	824	223
25°	296	139
35°	64	43
45°	11	9
55°	3	3
65°	1	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224759

CATALOG NUMBER: LSSQWM2B05FL409730D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1243.4
2.5°	1237.9
5°	1216.1
7.5°	1160.8
10°	1068.7
12.5°	958.1
15°	824.4
17.5°	678.3
20°	533.7
22.5°	404.7
25°	295.5
27.5°	208.1
30°	142.6
32.5°	96.2
35°	63.5
37.5°	38.2
40°	23.9
42.5°	16.4
45°	10.9
47.5°	7.5
50°	5.5
52.5°	4.8
55°	3.4
57.5°	2.7
60°	2.7
62.5°	2.0
65°	1.4
67.5°	1.4
70°	1.4
72.5°	1.4
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)