

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224706

Luminaire Tested: **LSR2B05FL408035D010 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224706
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B05FL408035D010 2LBD*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 773.0 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224706

CATALOG NUMBER: LSR2B05FL408035D010 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224706

CATALOG NUMBER: LSR2B05FL408035D010 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86	86	86	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79	79	79	79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	699818
5°	687055
10°	610750
15°	480330
20°	319624
25°	183521
30°	92674
35°	43598
40°	17546
45°	8710
50°	4761
55°	3377
60°	3099
65°	1833
70°	2265
75°	1497
80°	2231
85°	0



TEST NUMBER: P224706

CATALOG NUMBER: LSR2B05FL408035D010 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.8	20.9
10°-20°	324.5	42.0
20°-30°	201.9	26.1
30°-40°	62.1	8.0
40°-50°	13.6	1.8
50°-60°	4.9	0.6
60°-70°	2.5	0.3
70°-80°	1.4	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	688.1	89.0
0°-40°	750.2	97.0
0°-60°	768.7	99.4
0°-90°	773.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	773.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1807	
5°	1767	162
15°	1198	324
25°	429	202
35°	92	62
45°	16	14
55°	5	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224706

CATALOG NUMBER: LSR2B05FL408035D010 2LBD*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1806.7
2.5°	1798.7
5°	1767.0
7.5°	1686.7
10°	1552.8
12.5°	1392.2
15°	1197.8
17.5°	985.6
20°	775.4
22.5°	588.0
25°	429.4
27.5°	302.4
30°	207.2
32.5°	139.8
35°	92.2
37.5°	55.5
40°	34.7
42.5°	23.8
45°	15.9
47.5°	10.9
50°	7.9
52.5°	6.9
55°	5.0
57.5°	4.0
60°	4.0
62.5°	3.0
65°	2.0
67.5°	2.0
70°	2.0
72.5°	2.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)